



Product: [10GX33](#) 

Life Cycle Status: Discontinued

10GX Category 6A Enhanced Cable, 4 Bonded-Pairs, U/UTP, CMP

Product Description

10GX Category 6A Enhanced Premise Horizontal Cable (625MHz), 4 Bonded-Pairs, 23 AWG Solid Bare Copper Conductors, U/UTP, Plenum-CMP, Flamarrest® PVC-LS Jacket

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, Ethernet up to 10GBASE-T, HDBaseT, PoE++, PoE+, PoE
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

Product Life Cycle

Life Cycle:	Discontinued - the product is no longer manufactured
Discontinuation Announcement Date:	2021-12-06

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
23 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
FEP - Fluorinated Ethylene Propylene	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown
Bonded-Pair:	Yes

Outer Jacket

Separator	Material	Material Trade Name	Nom. Diameter	Ripcord
Double H Cross-Web (Patented RoundFlex®)	PVC - Polyvinyl Chloride	Flamarrest®	0.295 in (7.49 mm)	Yes
Overall Cable Diameter (Nominal):	0.295 in (7.49 mm)			

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
74 Ohm/km (23 Ohm/1000ft)	90 pF/100m

Delay

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
100 MHz	537.6 ns/100m	30 ns/100m	68%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation) [dB/100m]	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]	Min. PSANEXT [dB]	Min. PSAACRF [dB]	Min. TCL [dB]	Min. ELTCTL [dB]
1	2.1	75.3	73.3	73.3	71.3	70.8	68.8	20.0	100 ± 15	100 ± 15	67.0	67.0	48.0	43.0
4	3.8	66.3	64.3	62.5	60.5	58.8	56.8	23.0	100 ± 15	100 ± 10.4	67.0	67.0	48.0	41.0

8	5.3	61.8	59.8	56.4	54.4	52.7	50.7	24.5	100 ± 15	100 ± 8	67.0	61.1	48.0	24.9
10	5.9	60.3	58.3	54.4	52.4	50.8	48.8	25.0	100 ± 15	100 ± 7.3	67.0	59.2	48.0	23.0
16	7.5	57.2	55.2	49.8	47.8	46.7	44.7	25.0	100 ± 15	100 ± 5.7	67.0	55.1	46.0	18.9
20	8.4	55.8	53.8	47.4	45.4	44.8	42.8	25.0	100 ± 15	100 ± 5	67.0	53.2	45.0	17.0
25	9.4	54.3	52.3	45.0	43.0	42.8	40.8	25.0	100 ± 15	100 ± 5	67.0	51.2	44.0	15.0
31.25	10.5	52.9	50.9	42.4	40.4	40.9	38.9	25.0	100 ± 15	100 ± 5	67.0	49.3	43.1	
62.5	15.0	48.4	46.4	33.4	31.4	34.9	32.9	25.0	100 ± 15	100 ± 5	66.6	43.3	40.0	
100	19.1	45.3	43.3	26.2	24.2	30.8	28.8	25.0	100 ± 15	100 ± 5	63.5	39.2	38.0	
200	27.6	40.8	38.8	13.2	11.2	24.8	22.8	21.0	100 ± 22	100 ± 5	59.0	33.2	35.0	
250	31.1	39.3	37.3	8.3	6.3	22.8	20.8	20.5	100 ± 32	100 ± 5	57.5	31.2	34.0	
300	34.3	38.1	36.1	3.9	1.9	21.3	19.3	20.1	100 ± 32	100 ± 5	56.3	29.7	33.2	
350	37.2	37.1	35.1			19.9	17.9	19.8	100 ± 32	100 ± 5	55.3	28.3	32.6	
400	40.1	36.3	34.3			18.8	16.8	19.5	100 ± 32	100 ± 5	54.5	27.2	32.0	
450	42.7	35.5	33.5			17.7	15.7	18.9	100 ± 32	100 ± 5	53.7	26.1	31.5	
500	45.3	34.8	32.8			16.8	14.8	18.4	100 ± 32	100 ± 5	53.0	25.2	31.0	
550	47.7	34.2	32.2			16.0	14.0	18.0	100 ± 32	100 ± 5	52.4	24.4		
600	50.1	33.6	31.6			15.2	13.2	17.6	100 ± 32	100 ± 5	51.8	23.6		
625	51.2	33.4	31.4			14.9	12.9	17.4	100 ± 32	100 ± 5	51.6	23.3		
750	56.7	32.2	30.2			13.3	11.3	16.5			50.4	21.7		
860	61.2	31.3	29.3			12.1	10.1	15.8			49.5	20.5		

Voltage

UL Voltage Rating
300 V (CMP), 300 V (CL3P)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
105°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
0.6 in (15 mm)	3.0 in (76 mm)

Max. Pull Tension:	40 lbs (18 kg)
Bulk Cable Weight:	46 lbs/1000ft (68 kg/km)

Standards and Compliance

Environmental Suitability:	Plenum, Indoor
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMP, CMP-LP (0.6A), CL3P-LP (0.6A)
CEC / C(UL) Compliance:	CMP.
ICEA Compliance:	S-116-732
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6A
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6A
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
CENELEC Compliance:	Segregation class according EN50174-2 = a
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	10GX32

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 625 MHz are for Engineering Information Only. 0.295" Cable Dimension per TIA 6@1 Equivalent Diameter. Print includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	--

History

Update and Revision:	Revision Number: 0.683 Revision Date: 07-28-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
10GX33 D151000	Blue	Reel	1,000 ft	612825102335	C
10GX33 0081000	Gray	Reel	1,000 ft	612825102359	C
10GX33 0091000	White	Reel	1,000 ft	612825102366	C
10GX33 0041000	Yellow	Reel	1,000 ft	612825102342	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.