

29505 Multi-Conductor - 1000V UL Flexible Motor Supply Cable



For more Information
please call

1-800-Belden1

**General Description:**

4-cond. (3)stranded tinned copper circuit conductors plus (1)ground wire , XLP insulation, Overall Duofoil® (100% cov.) plus a tinned copper braid shield (85% cov.) , tinned copper sectioned drain wire, sun-&oil-resistant , sun-&oil-resistant PVC jacket.

Usage (Overall)

Suitable Applications:

AC Motor Drives, VFD, Variable Frequency Drives

Physical Characteristics (Overall)**Conductor**

AWG:

# Conductors	AWG	Stranding	Conductor Material
3	6	7x19x27	TC - Tinned Copper

Total Number of Conductors: 3

Ground Wire

Ground Wire (Y/N):	Y
Ground Wire AWG:	6
Ground Wire Stranding:	7x19x27
Ground Wire Conductor Material:	TC - Tinned Copper
Ground Wire Insulation Material:	PVC - Polyvinyl Chloride

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
XLP - Cross Linked Polyolefin	1.524

Insulation Resistance: 300 Megaohms/1000 ft.

Insulation Color Code Chart:

Number	Color
1	Black and Numbered 1
2	Black and Numbered 2
3	Black and Numbered 3
4	Green/Yellow

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	85

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
12 (4x)	65x30	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
-----------------------	--------------------------

29505 Multi-Conductor - 1000V UL Flexible Motor Supply Cable

PVC - Polyvinyl Chloride	2.362
--------------------------	-------

Overall Cable

Overall Nominal Diameter:	26.111 mm
----------------------------------	-----------

Mechanical Characteristics (Overall)

Wet Temperature Range:	-40°C To +90°C
Dry Temperature Range:	-40°C To +90°C
Bulk Cable Weight:	1206.930 Kg/Km
Max. Recommended Pulling Tension:	5426.804 N
Min. Bend Radius/Minor Axis:	209.550 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	TC-ER, Unlisted Singles, WTTC
NEC Articles:	336 - ER
CEC/C(UL) Specification:	600V Type CIC TC
CSA Specification:	1000 V AWM I/II A/B
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/13/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
PMSHA Specification:	P-07 KA070003
Other Specification:	1000V UL Flexible Motor Supply Cable

Flame Test

UL Flame Test:	UL1685 UL Loading
CSA Flame Test:	FT4
IEEE Flame Test:	1202, IEEE 383 Vertical Tray Flame Test (70,000 BTU)

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes
Sunlight Resistance:	Yes
Oil Resistance:	Yes

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)
56

Nom. Inductance:

Inductance (µH/m)
0.561051

29505 Multi-Conductor - 1000V UL Flexible Motor Supply Cable

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
108.273

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
196.86

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
1.34521

Max. Operating Voltage - UL:

Voltage
1000 V RMS (Flexible Motor Supply Cable)
600 V RMS (NEC Type TC)

Max. Operating Voltage - Other:

Voltage	Description
1000 V RMS	CSA AWM I/II A/B

Max. Recommended Current:

Current
75 Amps per conductor @ 30°C (per NEC)

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
29505 0101000	1,000 FT	911.000 LB	BLACK	C Z	3 #6 XLPE, #6 PVC SH HMF
29505 010250	250 FT	212.750 LB	BLACK	C Z	3 #6 XLPE, #6 PVC SH HMF
29505 0103500	3,500 FT	3,045.000 LB	BLACK	C Z	3 #6 XLPE, #6 PVC SH HMF

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 4 Revision Date: 04-04-2016

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).