



Product: [6302UL](#)

Fire Alarm, #18-4c BC, FPLP

Product Description

Fire Alarm Cable, Plenum-FPLP, 4-18 AWG stranded bare copper conductors with Flamarrest® insulation, Flamarrest® jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Fire Alarm, Monitor/Detection, Circuits: Audio, Control, Initiating, Notification
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
18	7x26	BC - Bare Copper	4

Conductor Count:	4
------------------	---

Insulation

Material	Material Trade Name	Nominal Wall Thickness
PVC - Polyvinyl Chloride	Flamarrest®	0.009 in

Color Chart

Number	Color
1	Black
2	Red
3	Brown
4	Blue

Outer Shield

Material
No Shield

Outer Jacket

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	Flamarrest®	0.185 in	0.015 in	Yes

Construction and Dimensions

Cabling

Twists
4 twist/ft

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
6.5 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
28.25 pF/ft

Current

Max. Recommended Current [A]
6.4 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Operating Temperature Range:	0°C To +75°C
------------------------------	--------------

Mechanical Characteristics

Bulk Cable Weight:	30 lbs/1000ft
Max. Pull Tension:	89.5 lbs
Min. Bend Radius/Minor Axis:	1.875 in

Standards

NEC Articles:	Article 760
NEC/(UL) Compliance:	FPLP

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262 Plenum Flame Test (UL910)
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Related Part Numbers

Non-Plenum Number:	5302UL
--------------------	--------

Variants

Item #	Color	UPC
6302UL 002U1000	Red	612825175421

History

Update and Revision:	Revision Number: 0.167 Revision Date: 05-05-2023
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.