



Product: [6340FT](#)

Thermostat & Control, #18-2c, TC, O/A Foil, CMP

Product Description

Thermostat & Control Cable, Plenum-CMP, 1-18 AWG stranded tinned copper pair with foam FEP insulation, Beldfoil® shield, Flamarrest® jacket

Technical Specifications

Product Overview

Suitable Applications:	Thermostat, Control, Noisy Environment
------------------------	--

Construction Details

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	18	7x26	TC - Tinned Copper

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene (Foam)	0.0265 in (0.673 mm)	0.099 in (2.5 mm)	Black and White

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (7x26) TC

Material	Nom. Thickness	Nom. Diameter
FEP - Fluorinated Ethylene Propylene	0.015 in (0.38 mm)	0.232 in

Electrical Characteristics

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Velocity of Prop.	Max. Current
7.1 Ohm/1000ft	16.9 pF/ft (55.4 pF/m)	78%	4.8 Amps per Conductor at 25°C

UL Voltage Rating
300 V

Mechanical Characteristics

UL Temperature	Operating
75°C	-20°C To +75°C

Stationary Min.	Installation Min.
2.32 in (58.9 mm)	2.32 in

Max. Pull Tension:	67 lbs (30 kg)
--------------------	----------------

Bulk Cable Weight:	30 lbs/1000ft
--------------------	---------------

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark

History

Update and Revision:	Revision Number: 0.335 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
6340FT 0011000	Brown	612825176244	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.