

**M12 male 0° / M12 female 0° A-cod.**

TPE 4x18/19AWG ye UL/CSA. ITC/PLTC 3m

Art.No.: 7700-40021-1500300

Weight: 0.264

Country of origin: US

Model designation: MSBL0-A-T150\_3.0


**Advantages of our connectors:**

Our connectors are versatile and specially optimised for industrial environments. All connectors are 100% tested during the manufacturing process to ensure the highest quality and reliability.





The contacts are gold-plated, which ensures optimum conductivity. Thanks to the high degree of protection, the connectors are ideal for demanding industrial environments. They are also vibration-resistant - this is ensured by the union nut with vibration protection.

Our connectors are resistant to oils and cooling lubricants, but resistance to aggressive media should be tested for each specific application. Different cable lengths available [on request](#)

If you are missing technical information? Please feel free to use our [dictionary](#) to find more technical details.

**Product details:****Cable is approved for 600 V****Male straight – female straight****M12 – M12, 4-pole****USA****Cable is approved for 600 V****Plastic housings with good resistance against chemicals and oils.****The resistance to aggressive media should be individually tested for your application. Further details on request.****Further cable lengths on request.****[Link to Product](#)****Illustration**

|   |    |     |
|---|----|-----|
| 1 | BN | C 1 |
| 2 | WH | C 2 |
| 3 | BU | C 3 |
| 4 | BK | C 4 |



Product may differ from Image



|                   |        |
|-------------------|--------|
| Cable length      | 3 m    |
| Side 1            |        |
| Tightening torque | 0,6 Nm |

|                                        |                   |
|----------------------------------------|-------------------|
| Mounting method                        | inserted, screwed |
| Family construction form               | M12               |
| Thread                                 | M12 x 1           |
| Gender                                 | male              |
| Cable outlet                           | straight          |
| Coding                                 | A                 |
| No. of poles                           | 4                 |
| Width across flats                     | SW13              |
| Side 2                                 |                   |
| Tightening torque                      | 0,6 Nm            |
| Mounting method                        | inserted, screwed |
| Family construction form               | M12               |
| Thread                                 | M12 x 1           |
| Gender                                 | female            |
| Cable outlet                           | straight          |
| Coding                                 | A                 |
| No. of poles                           | 4                 |
| Width across flats                     | SW13              |
| Commercial data                        |                   |
| ECLASS-6.0                             | 27279218          |
| ECLASS-6.1                             | 27279218          |
| ECLASS-7.0                             | 27279218          |
| ECLASS-8.0                             | 27279218          |
| ECLASS-9.0                             | 27060311          |
| ECLASS-10.1                            | 27060311          |
| ECLASS-11.1                            | 27060311          |
| ECLASS-12.0                            | 27060311          |
| ETIM-5.0                               | EC001855          |
| ETIM-6.0                               | EC001855          |
| ETIM-7.0                               | EC001855          |
| ETIM-8.0                               | EC001855          |
| customs tariff number                  | 85444290          |
| customs tariff number                  | 85444290          |
| GTIN                                   | 4048879518284     |
| GTIN                                   | 4048879518284     |
| Packaging unit                         | 1                 |
| Packaging unit                         | 1                 |
| Electrical data   Supply               |                   |
| Operating voltage AC max.              | 250 V             |
| Operating voltage DC max.              | 250 V             |
| Operating voltage AC (UL-listed)       | 30 V              |
| Operating voltage DC (UL-listed)       | 30 V              |
| Current operating per contact max.     | 4 A               |
| Device protection   Electrical         |                   |
| Degree of protection (EN IEC 60529)    | IP65, IP67, IP66K |
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 2,5 kV            |
| Material group (IEC 60664-1)           | I                 |
| Mechanical data                        |                   |
| Contour for corrugated hose            | without           |
| Mechanical data   Material data        |                   |

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-05-14

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

|                                                   |                                                                                                                                                |
|---------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
| Color housing                                     | black                                                                                                                                          |
| Coating locking                                   | Nickeled                                                                                                                                       |
| Color contact carrier                             | green                                                                                                                                          |
| Locking material                                  | Zinc die-casting                                                                                                                               |
| <b>Mechanical data   Mounting data</b>            |                                                                                                                                                |
| Mounting method                                   | inserted, screwed, Shaking protection                                                                                                          |
| <b>Environmental characteristics   Climatic</b>   |                                                                                                                                                |
| Operating temperature min.                        | -30 °C                                                                                                                                         |
| Operating temperature max.                        | 85 °C                                                                                                                                          |
| Additional condition temperature range            | depending on cable quality                                                                                                                     |
| <b>Important installation notes</b>               |                                                                                                                                                |
| Note on strain relief                             | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                            |
| Note on bending radius                            | Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| <b>Conformity</b>                                 |                                                                                                                                                |
| Product standard                                  | DIN EN 61076-2-101 (M12)                                                                                                                       |
| <b>Installation   Cable</b>                       |                                                                                                                                                |
| wire arrangement                                  | brown, black, blue, white                                                                                                                      |
| Cable identification                              | 150                                                                                                                                            |
| Jacket Color                                      | yellow                                                                                                                                         |
| Amount stranding                                  | 1                                                                                                                                              |
| Stranding                                         | 4 wires twisted                                                                                                                                |
| wire arrangement                                  | brown, black, blue, white                                                                                                                      |
| Cable weight                                      | 92,4 g/m                                                                                                                                       |
| Material jacket                                   | TPE                                                                                                                                            |
| Freedom from ingredients (jacket)                 | lead-free, CFC-free, halogen-free                                                                                                              |
| Outer-diameter (jacket)                           | 7,21 mm                                                                                                                                        |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                                                                                                          |
| Material wire insulation                          | PVC                                                                                                                                            |
| Amount wires                                      | 4                                                                                                                                              |
| Outer diameter insulation                         | 1,93 mm                                                                                                                                        |
| Outer diameter tolerance core insulation          | ± 5 %                                                                                                                                          |
| Ingredient freeness wire insulation               | lead-free, CFC-free                                                                                                                            |
| Amount strands (wire)                             | 19                                                                                                                                             |
| Diameter of single wires                          | 18 AWG                                                                                                                                         |
| Conductor crosssection (wire)                     | 18 AWG                                                                                                                                         |
| Material conductor wire                           | Stranded copper wire, bare                                                                                                                     |
| Nominal voltage AC max.                           | 600 V                                                                                                                                          |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                                                                                                              |
| Current load capacity min. wire                   | 9,6 A                                                                                                                                          |
| Electrical resistance line constant wire          | 22,5 Ω/km @ 20 °C                                                                                                                              |
| AC withstand voltage (wire - wire)                | 4 kV @ 60 s                                                                                                                                    |
| Power frequency withstand voltage (wire - jacket) | 4 kV @ 60 s                                                                                                                                    |
| Min. operating temperature (static)               | -40 °C                                                                                                                                         |
| Max. operating temperature (fixed)                | 105 °C                                                                                                                                         |
| Operating temperature min. (dynamic)              | -20 °C                                                                                                                                         |
| Operating temperature max. (dynamic)              | 90 °C                                                                                                                                          |
| Flame resistance                                  | IEC 60332-2-2   UL 1581 § 1090   UL 1581 § 1100 FT2                                                                                            |
| chemical resistance                               | Good, application-related testing                                                                                                              |
| Gasoline resistance                               | Good, application-related testing                                                                                                              |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404                                                                                           |
| Bending radius (fixed)                            | 10 x Outer diameter                                                                                                                            |

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-05-14

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

|                                 |                          |
|---------------------------------|--------------------------|
| Bending radius (dynamic)        | 15 x Outer diameter      |
| No. of bending cycles (C-track) | 10 Mio.                  |
| No. of torsion cycles           | 3 Mio.                   |
| Torsion stress                  | $\pm 180^\circ/\text{m}$ |