



Product: [8678](#)

Electronic, 2 C #10 Str BC, PVC Ins, PVC Jkt

[Request Sample](#)

Product Description
Electronic, 2 Conductor 10AWG (19x23) Bare Copper, PVC Insulation, PVC Jkt

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio
------------------------	---

Construction Details

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	10 AWG	19x23	BC - Bare Copper

Element	Material	Nom. Thickness	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	Brown, Red

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.025 in (0.64 mm)	0.225 x 0.400 in

Table Notes:	Insulated conductors lay in parallel under jacket
--------------	---

Electrical Characteristics

Element	Max. Current
Conductor(s)	16 Amps per Conductor at 25°C

Voltage Rating
300 V

Mechanical Characteristics

Operating
-20°C to +75°C

Stationary Min.	Installation Min.
2.3 in (58 mm)	2.3 in (58 mm)

Max. Pull Tension:	235.6 lbs (106.9 kg)
Bulk Cable Weight:	95 lbs/1000ft (140 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.332 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8678 060500	Chrome	Reel	500 ft	612825214045	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.