

M12 fem. recept. D-cod. rear/RJ45 male 0° shielded




TPE 22AWG SF/UTP CAT5e gn UL/CSA. ITC/PLTC 8m



Art.No.: 7700-44851-S7V0800

Weight: 0.636


Country of origin: DE

Model designation: MSDBFH-RA-TS7V_8.0-ZS

Link to Product**Illustration**



Product may differ from Image



Header	
Cable length	8.0 m
Side 1	
Family construction form	M12
No. of poles	4
Coding	D
Mounting method	inserted, screwed
Degree of protection (EN IEC 60529)	IP67
Side 2	
Family construction form	RJ45
No. of poles	4
Mounting method	pluggable
Degree of protection (EN IEC 60529)	IP20
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7700-44851-S7V0800
GTIN	4048879700986
ECLASS-6.0	27279220
ECLASS-6.1	27279220

ECLASS-7.0	27440103
ECLASS-7.1	27440103
ECLASS-8.0	27440103
ECLASS-8.1	27440103
ECLASS-9.0	27440103
ECLASS-9.1	27440109
ECLASS-10.0.1	27440109
ECLASS-10.1	27440103
ECLASS-11.0	27440109
ECLASS-11.1	27440103
ECLASS-12.0	27440103
ECLASS-13.0	27440109
ECLASS-14.0	27440109
ETIM-5.0	EC002599
ETIM-6.0	EC002599
ETIM-7.0	EC002599
ETIM-8.0	EC002599
EAN	4048879700986

Electrical data | Supply

Operating voltage DC max.	60 V
Current operating per contact max.	1.5 A

Industrial communication

Data transmission rate max.	100 MBit/s
Transfer parameters	CAT5, Class D (ISO/IEC 11801:2002), (EN 50173-1)

Industrial communication | Ethernet functionality

duplex	Full duplex
--------	-------------

Installation | Connection

Width across flats	SW19
--------------------	------

Device protection | Electrical

Protection NEMA	6P, 4, 3
Pollution Degree	3
Rated surge voltage	1 kV
Material group (IEC 60664-1)	I

Mechanical data

Contour for corrugated hose	without
-----------------------------	---------

Mechanical data | Material data

Locking material	Brass
Coating locking	nickel plated

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Installation | Cable

Cable identification	S7V
Amount stranding	2
Stranding	Wires
Amount stranding (type 2)	1

Stranding (type 2)	Stranded joints
Cable shielding (type)	copper braid, tinned
Cable shielding (coverage)	75 %
Banding	Foil
Wire arrangement	(, white, blue,), orange, yellow
Cable weight	74.8
Material wire insulation	HDPE
Amount wires	4
Outer diameter insulation	1.47 mm
Outer diameter tolerance core insulation	± 0.05 mm
Ingredient freeness wire insulation	CFC-free, lead-free
Amount strands (wire)	19
Diameter of single wires	22 AWG
Conductor crosssection (wire)	22 AWG
Material conductor wire	copper stranded wire, tinned
Outer-diameter (jacket)	7.87 mm
Tolerance outer diameter (sheath)	± 5 %
Material jacket	TPE
Freedom from ingredients (jacket)	CFC-free, lead-free
Electrical resistance line constant wire	45.1 Ω/km
Nominal voltage AC max.	600 V
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity min. wire	4.8 A
Min. operating temperature (static)	-40 °C
Max. operating temperature (fixed)	80 °C
Operating temperature min. (dynamic)	-40 °C
Operating temperature max. (dynamic)	80 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C
Bending radius (dynamic)	8 × Outer diameter
No. of bending cycles (C-track)	35 Mio.
No. of torsion cycles	5 Mio.
Torsion stress	180 °/m