



Product: [9618](#)

RS232, #24-37c, SR-PVC, O/A Foil+Braid, PVC Jkt, CMG

Product Description

Computer EIA RS-232 Cable, 24 AWG stranded (7x32) tinned copper conductors, semi-rigid PVC insulation, overall Beldfoil® (100% coverage) + tinned copper braid shield (65% coverage), PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	RS-232 applications; Computer Communications; Low Voltage Analog signals (4-20ma, 0-10v, ...); Low Voltage Digital control (24v, ...); Line Level Audio; Panel Wiring
------------------------	---

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Conductor(s)	37	24 AWG	7x32	TC - Tinned Copper

Insulation				
Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	SR-PVC - Polyvinyl Chloride (Semi-Rigid)	0.011 in (0.28 mm)	0.044 in (1.1 mm)	Black, White, Red, Green, Orange, Blue, White/Black Stripe, Red/Black Stripe, Green/Black Stripe, Orange/Black Stripe, Blue/Black Stripe, Black/White Stripe, Red/White Stripe, Green/White Stripe, Blue/White Stripe, Black/Red Stripe, White/Red Stripe, Orange/Red Stripe, Blue/Red Stripe, Red/Green Stripe, Orange/Green Stripe, Black/White/Red Stripes, White/Black/Red Stripes, Red/Black/White Stripes, Green/Black/White Stripes, Orange/Black/White Stripes, Blue/Black/White Stripes, Black/Red/Green Stripes, White/Red/Green Stripes, Red/Black/Green Stripes, Green/Black/Orange Stripes, Orange/Black/Green Stripes, Blue/White/Orange Stripes, Black/White/Orange Stripes, White/Red/Orange Stripes, Orange/White/Blue Stripes, White/Red/Blue Stripes

Outer Shield		
Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%
Braid	Tinned Copper (TC)	65%

Outer Jacket		
Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.040 in (1.0 mm)	0.411 in (10.4 mm)
Overall Cable Diameter (Nominal):		0.411 in (10.4 mm)

Electrical Characteristics

Electricals				
Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	25 Ohm/1000ft	30 pF/ft (98 pF/m)	55 pF/ft (180 pF/m)	1 Amp per Conductor at 25°C

Voltage	
UL Voltage Rating	
300 V (CMG), 300 V (UL AWM 2464)	

Mechanical Characteristics

Temperature	
UL Temperature	Operating

80°C	-30°C to +80°C
------	----------------

Bend Radius

Stationary Min.	Installation Min.
4.1 in (100 mm)	4.1 in (100 mm)

Max. Pull Tension:	241 lbs (109 kg)
Bulk Cable Weight:	122 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.499 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9618 060100	Chrome	Reel	100 ft	612825256588	
9618 060500	Chrome	Reel	500 ft	612825256601	C
9618 0601000	Chrome	Reel	1,000 ft	612825256595	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.