


AX102243 Faceplates and Panels - KeyConnect ST Module Multimode/Singlemode



For more Information
please call

1-800-Belden1



General Description:

KeyConnect Module ST Multimode/Singlemode

Usage (Overall)

Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room
Related Parts:	- Compatible KeyConnect-style Faceplate and Patch Panel

Physical Characteristics (Connectivity)

Access

Front Connection:	Flush
-------------------	-------

Dimensions

Dimensions:

Height (mm)	Width (mm)	Depth (mm)
21.590	16.510	20.066

Materials

Materials:

Description	Type	Material
Insert		Plastic - UL94V-0
Connector Body	ST	Metal
Sleeve		Zirconia-Ceramic

Color

Color:	Elec. White
--------	-------------

Weight

Weight:	0.005 kg
---------	----------

Packaging

Packaging:	10 units packaged in a plastic bag.
------------	-------------------------------------

Mechanical Characteristics (Connectivity)

Footprint/Type:	KeyConnect
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2006
MIL Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For additional information about this product, visit our web site at <http://www.belden.com>.

Product Family

Part Numbers:

Item Number	Color
AX102242	Almond
AX102243	Elec. White
AX102244	Black

Put Ups and Colors:

METRIC MEASUREMENT VERSION

AX102243 Faceplates and Panels - KeyConnect ST Module Multimode/Singlemode

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX102243	1 EA	0.014 KG			KCONN ST MODULE MM/SM E-WH

Revision Number: 0 Revision Date: 03-20-2017

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.