

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	38[mm]
Max. Air Flow:	66.39[CFM]
Max. Air Flow:	1.88[m3 per min]
Max. Static Pressure:	3.71[In H2O]
Max. Static Pressure:	925[Pa]
Fan Speed:	17000[RPM]
Noise:	63.5[dB]
Life Expectancy:	40 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	10.8[V]
Operating Voltage - Upper:	13.2[V]
Current:	1.65[A]
Input Power:	19.8[W]
Mass:	123[g]
Tach / Locked Rotor Output:	Tach Output
Status:	Active