

Detailed Specifications

Frame Width:	25[mm]
Frame Height:	25[mm]
Frame Length:	17[mm]
Steps per Rev.:	24
Step Angle:	15[degrees]
Drive Sequence:	bipolar constant current
Drive Voltage:	24[V]
Rated Current per Phase:	600[A]
Resistance:	8[Ohms]
Magnet Type:	MS70
Magnet Material:	bonded Nd-Fe-B
Holding Torque:	18[mN per m]
Max Speed:	2200[pps]
Max Speed:	5500[rpm]