

6

5

4

3





2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/22/12	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED
PCB LAYOUT

PACKAGED ON TAPE & REEL

Positions: 02 thru 15

A=.059 [1.50] X No. of (Positions -1)

B=.059 [1.50] X No. of (Positions -1) + .110 [2.80]

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 350 V AC/DC

Current rating: 3 V AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: MX1.5mm WAFER 90°, SURFACE MOUNT

2 THRU 15 POSITIONS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED							
INCHES				Holes			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	AY		2/22/12	SIZE	PART NO.	15SH-B-XX-TR-SMT-T/R	REV.
CHECKED	CC		2/22/12	X			-
APPROVED				REF:	SCALE: NTS	SHEET 1 OF 1	