





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/14/09	
A		REVISED DIM.	11/6/13	AY/GC



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Plating: Gold flash over Nickel underplate overall
Electrical: Current rating: 1 Amp max
Contact resistance: 20 mohms max
Insulation resistance: 5,000 Mohms min @ 500 VDC
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant



Positions: 2 thru 40
A = .079 [2.00] x No. of Positions
B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES	HOLES			.079 [2.00] SINGLE ROW PIN HEADER SURFACE MOUNT, TYPE B			
.X ± .10	ØX ± .10	DATE					
.XX ± .020	ØXX ± .015						
.XXX ± .015	ØXXX ± .010						
APPROVALS							
DRAWN	DY	7/14/09					
CHECKED							
APPROVED							
TITLE				SIZE	PART NO.	REV.	
				X	2PH1-XX-UA-SMT-B	A	
REF:				S00039T	SCALE: NTS	SHEET 1 OF 1	