

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev

AWO #

Description



Date

Appr


-

RELEASED

10/28/13



Recommended PCB Layout



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: Natural

Contacts: Phosphor Bronze

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 600 V

Current rating: 2~4P: 13A, 6~10P: 11A

Dielectric withstanding voltage: 5000 VAC for 1 minute

Temperature Rating:

-55°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 10

A = .250 [6.35] X No. of Positions per row + .050 [1.27]

B = .250 [6.35] X No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS

DATE

DRAWN

AY

10/28/13

CHECKED

GC

10/28/13

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE WIRE TO BOARD, FEMALE, 6.35mm PITCH
SINGLE ROW TYPE

SIZE

X

PART NO.

DME-F-XX-S-S

REV.

-

REF: S00123T

SCALE: NTS

SHEET 1 OF 1