





APPROVED: _____
DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating: Gold flash over Nickel underplate overall
Electrical: Current rating: 1 Amp max.
Contact resistance: 20 mohms max.
Insulation resistance: 1,000 Mohms min.
Dielectric withstanding voltage: 500 VAC/DC for 1 minute
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/25/05	
A		REDRAWN	8/3/12	
B		REVISED DIM.	06/13/13	
C		UPDATE DRAWING	9/10/15	AV/RT

Positions: 04 thru 100
A = .050 [1,27] x No. of Positions per Row +.016 [0,40]
B = .050 [1,27] x No. of Spoces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØXX	± .10	.XX	± .020	ØXXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	SS	5/25/05					
CHECKED							
APPROVED							
				TITLE			
				.050 x .100 DUAL ROW RECEPTACLE STRIP			
				LOW PROFILE			
				ADAM TECH			
				909 Railway Avenue, Union, NJ 07083			
				Phone: 908-687-5000 Fax: 908-687-5710			
				SIZE			
				X			
				PART NO.			
				HRS-2B-XX-GA			
				REV.			
				C			