





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	-	RELEASED	8/13/12	
A	-	REVISED DIM.	10/3/12	



PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating: Gold flash over Nickel underplate overall.
Electrical: Current rating: 1 Amp max.
Contact resistance: 15 mohms max. initial
Insulation resistance: 5,000 Mohms min.
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant

Positions: 6 thru 100
A = .031 [0.80] x No. of Positions Per Row
B = .031 [0.80] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES	HOLES	ØXX	±.10	SIZE	PART NO.	REV.	
.X ±.10	ØXX ±.10	XX ±.020	ØXXX ±.015	X	SPH2-XX-U-SMT	A	
.XXX ±.015	ØXXX ±.010	APPROVALS	DATE	REF:	S00039T	SCALE:	NIS
DRAWN	TW	8/13/12		SIZE			
CHECKED	AY	8/13/12		REV.			
APPROVED				SHEET	1	OF	1