


Rev	AWO #	Description	Date	Appr
-		RELEASED	6/9/05	
A		REDRAWN	6/10/14	AY/CH
B		ADDED SPEC.	6/12/14	HR/YC

APPROVED: _____
DATE: _____ TITLE: _____



REPLACE XX IN PART NUMBER
WITH TOTAL # OF SCREW POLES

Screw	ADAM P/N	Screw	ADAM P/N
4	TBH-04-01-B	30	TBH-30-01-B
6	TBH-06-01-B	32	TBH-32-01-B
8	TBH-08-01-B	34	TBH-34-01-B
10	TBH-10-01-B	36	TBH-36-01-B
12	TBH-12-01-B	38	TBH-38-01-B
14	TBH-14-01-B	40	TBH-40-01-B
16	TBH-16-01-B	42	TBH-42-01-B
18	TBH-18-01-B	44	TBH-44-01-B
20	TBH-20-01-B	46	TBH-46-01-B
22	TBH-22-01-B	48	TBH-48-01-B
24	TBH-24-01-B	50	TBH-50-01-B
26	TBH-26-01-B	52	TBH-52-01-B
28	TBH-28-01-B		

SPECIFICATIONS:

Material: Insulator: Thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Brass, Tin Plated
Screws: Steel, Nickel Plated
Electrical: Insulation resistance: 500 Mohms min.
Dielectric withstanding voltage: 2,000 VAC for 1 minute
Mechanical: Wire range: 12 – 22 AWG
Environmental: Lead free, RoHS compliant

A = .325 [8.25] x No. of Screws per row + .079 [2.00]
B = .325 [8.25] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES				HOLES			
.X	± .10	Ø.X	± .10	TITLE . .325 [8.25] STACKED BARRIER BLOCK VERTICAL, PCB TAILS, BARRIER ENDS			
.XX	± .020	Ø.XX	± .015				
.XXX	± .015	Ø.XXX	± .010				
APPROVALS		DATE					
DRAWN		SS		6/9/05			
CHECKED						SIZE	
APPROVED						PART NO.	
				X		TBH-XX-01-B	
REF: S0003TT		SCALE: NTS		SHEET 1 OF 1		REV.	
						A	