



DATE: _____ TITLE: _____






Rev	AWO #	Description	Date	Appr
-		RELEASED	10/19/18	
A		UPDATE DIM.	12/26/24	WY/FH




PIN ASSIGNMENT											
A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GN	TX1	TX1	VBUS	CC1	D+	D-	RFU1	VBUS	R12	R12+	GN
GN	R17+	R17-	VBUS	RFU2	D-	D+	CC2	VBUS	TX2	TX2	GN
R12	R11	R10	R9	R8	R7	R6	R5	R4	R3	R2	R1




RECOMMENDED PCB LAYOUT
(TOP VIEW)



MATING CONDITION



SECTION U-U



SECTION T-T

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Copper Alloy
MID-Plate: Stainless Steel
Shell: Stainless Steel
Outer Shell: Stainless Steel

Plating:

Gold flash over Nickel underplate on contact area,
Matte Tin over Nickel underplate on solder tails.

Electrical:

Voltage rating: 20V

Current rating: 5A for VBUS Pins (A4, A9, B4, B9)

1.25A for GND Pins (A1, A12, B1, B12)

0.25A for Other Pins

Contact resistance: 40 mohms max for VBUS GND & Other Contact
50 mohms max After Environment Test.
Measure at 20mV, 100mA

Mechanical:

Insertion force: 5~20N

Withdrawal force: 8~20N

Durability: 10,000 cycles

Temperature Rating:

Operating temperature: -55°C to $+85^{\circ}\text{C}$

Environmental:

Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

	MM		ANGLE
X	± 0.50	X	± 1°
X.X	± 0.25		
X.XX	± 0.15		
X.XXX	± 0.10		

DRAWN	AY	10/19/18
CHECKED	TW	10/19/18
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM TECH

**909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710**

TITLE	UNIVERSAL SERIAL BUS, TYPE C, FEMALE, HYBRID TYPE, RIGHT ANGLE, H=3.63 MM
-------	--

SIZE X	PART NO. USB-C31-S-RA-CS12-BK-T/R	REV. A
REF: S00288T	SCALE: NTS	SHEET 1 OF 1