

Alternate Catalog No. AF12Z-30-10-30 Catalog No. 1SBL156001R3010

Description: AF12Z-30-10-30 24VDC Contactor

UPC No 3471523113596

Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors

AF12Z 3-pole contactors are used for controlling power circuits up to 690 V AC and 220 V DC. They are mainly used for controlling 3-phase motors, non-inductive or slightly inductive loads. AF12Z contactors with coil 30 include a 24 V DC electronic coil interface with a built-in surge suppression, obtaining a reduced holding coil consumption up to 1.7 W for a low panel energy consumption and a direct control by PLC-output ≥ 250 mA 24 V DC, without need of additional interface relay. Only AF...Z...-30 contactors need to respect the polarity on the coil terminals (A1+ and A2-). The AF... series 1-stack 3-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 3 main poles, 1 built-in auxiliary contact, front and side-mounted add-on auxiliary contact blocks. (mechanically-linked auxiliary contacts compliant with Annex L of IEC 60947-5-1. N.C. mirror contacts compliant with Annex F of IEC 60947-4-1) - Accessories: a wide range of accessories is available.

Representative Image

Descriptors

Category	AF Contactors
Block Contactor Type	3-Pole Contactor

Specifications

Product Type	AF
General Use Rating UL/CSA	(600 V AC) 28 A
Object Classification Code	Q
Terminal Type	Screw Terminals
Rated Control Circuit Voltage	DC Operation 24 V
Number of Main Contacts NO	3
Number of Main Contacts NC	0
Climatic Withstand	Category B according to IEC 60947-1 Annex Q
Resistance to Vibrations acc. to IEC 60068-2-6	5 ... 300 Hz 4 g closed position / 2 g open position
Number of Auxiliary Contacts NO	1
RoHS Status	Following EU Directive 2011/65/EU
Reference Ambient Air Temperature	Close to Contactor for Storage -60 ... +80 °C Close to Contactor without Thermal O/L Relay -40 ... +70 °C Close to Contactor Fitted with Thermal O/L Relay -25 ... +60 °C
Rated Operational Voltage	Auxiliary Circuit 690 V
Number of Auxiliary Contacts NC	0
Maximum Operating Altitude Permissible	3000 m
Rated Operational Current AC-1	(690 V) 40 °C 28 A (690 V) 60 °C 28 A (690 V) 70 °C 24 A (220 / 230 / 240 V) 3 KWT (380 / 400 V) 5.5 KWT
Rated Operational Power AC-3	(415 V) 5.5 KWT (440 V) 5.5 KWT (500 V) 7.5 KWT (690 V) 7.5 KWT

Specifications

Horsepower Rating UL/CSA	(220 ... 240 V AC) Three Phase 3 hp (440 ... 480 V AC) Three Phase 7-1/2 hp (550 ... 600 V AC) Three Phase 10 hp (120 V AC) Single Phase 1 hp (200 ... 208 V AC) Three Phase 3 hp (240 V AC) Single Phase 2 hp
Conventional Free-air Thermal Current	acc. to IEC 60947-5-1, q = 40 °C 16 A acc. to IEC 60947-4-1, Open Contactors q = 40 °C 35 A
Rated Operational Current AC-15	(220 / 240 V) 4 A (24 / 127 V) 6 A (500 V) 2 A (690 V) 2 A (400 / 440 V) 3 A
Rated Frequency	Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz Main Circuit 50Hz Main Circuit 60 Hz
Rated Short-time Withstand Current	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 150 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 35 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 60 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 300 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 80 A for 0.1 s 140 A for 1 s 100 A
Rated Operational Current AC-3	(220 / 230 / 240 V) 60 °C 12 A (380 / 400 V) 60 °C 12 A (415 V) 60 °C 12 A (440 V) 60 °C 12 A (500 V) 60 °C 12.5 A (690 V) 60 °C 9 A
Maximum Electrical Switching Frequency	AC-1 600 cycles per hour AC-2 / AC-4 300 cycles per hour AC-3 1200 cycles per hour AC-15 1200 cycles per hour DC-13 900 cycles per hour
Rated Insulation Voltage	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 690 V
Maximum Breaking Capacity	cos phi=0.45 (cos phi=0.35 for I _e > 100 A) at 440 V 250 A cos phi=0.45 (cos phi=0.35 for I _e > 100 A) at 690 V 106 A
Maximum Mechanical Switching Frequency	3600 cycles per hour
Operate Time	Between Coil De-energization and NC Contact Closing 22 ... 57 ms Between Coil De-energization and NO Contact Opening 17 ... 29 ms Between Coil Energization and NC Contact Opening 20 ... 35 ms Between Coil Energization and NO Contact Closing 27 ... 53 ms
Secondary Rated Impulse Withstand Voltage	6 kV
Connecting Capacity Main Circuit	Rigid 1/2x 1 ... 6 m ² Flexible with Ferrule 1/2x 0.75 ... 6 m ² Flexible with Insulated Ferrule 1x 0.75 ... 4 m ² /2x 0.75 ... 2.5 m ²
Rated Operational Current DC-13	(125 V) 0.55 A / 69 W (24 V) 6 A / 144 W (250 V) 0.27 A / 68 W (48 V) 2.8 A / 134 W (72 V) 1 A / 72 W (110 V) 0.55 A / 60 W (220 V) 0.27 A / 60 W (400 V) 0.15 A / 60 W (500 V) 0.13 A / 65 W (600 V) 0.1 A / 60 W
Connecting Capacity Control Circuit	Flexible with Ferrule 1/2x 0.75 ... 2.5 m ² Flexible with Insulated Ferrule 1x 0.75 ... 2.5 m ² /2x 0.75 ... 1.5 m ² Rigid 1/2x 1 ... 2.5 m ²
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 0.75 ... 2.5 m ² Flexible with Insulated Ferrule 1x 0.75 ... 2.5/2x 0.75 ... 1.5 m ² Rigid 1/2x 1 ... 2.5 m ²
Screw Terminal Type	Screw Terminals
Wire Stripping Length	Auxiliary Circuit 10 mm Control Circuit 10 mm Main Circuit 10 mm

Classifications

ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 6.0	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
ETIM 5.0	EC000066 - Magnet contactor, AC-switching

Dimensions

Product Net Weight	0.43 kg
Product Net Depth / Length	97 mm
Product Net Width	45 mm
Product Net Height	86 mm

Package Information

Package Level 1 Width	96 mm
Package Level 1 Height	50 mm
Package Level 1 Depth / Length	112 mm
Package Level 1 EAN	3471523113596
Package Level 1 Units	box 1 piece
Package Level 2 Width	51 mm
Package Level 2 Height	114 mm
Package Level 1 Gross Weight	0.475 kg
Package Level 2 Units	box 12 piece
Package Level 3 Units	576 piece
Package Level 2 Depth / Length	98 mm
Package Level 2 Gross Weight	5.7 kg

Ordering

Minimum Order Quantity	1
Customs Tariff Number	85364900