



Representative Image

Catalog No. THQL2125GFT**Description: THQL 2P 120/240V 25A GFCI SELF-TEST****UPC No 783164485356****Home > Circuit Breakers > Residential Circuit Breakers > Ground Fault**

Ground fault circuit interrupter (GFCI) breakers provide protection of receptacles located in the outdoors, in bathrooms, garages and spa areas. This applies to not only to new construction, but also to existing homes. When an electrical outlet is replaced in a location that requires ground-fault protection, the new outlet must be GFCI approved according to the NEC. All Q Line circuit breakers are one inch wide per pole, compact devices that feature: Quick-make / Quick-break mechanisms, common trip bars, and easy-to-spot trip indications to ensure safety and reliability as well as meets 2020 NEC standards. The THQL2125GFT breaker features ground fault interrupting technology, 2 poles, an ampere rating of 25 A, an interrupting rating of 10kAIC, and a voltage rating of 120/240V.

Descriptors

Category	Ground Fault
Product Line	Q-Line (Plug-In)

Specifications

Interrupting Capacity Rating	10 kAIC
Voltage	120/240 V
Neutral Connection	Pig Tail
Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	25 A
System Voltage	120/240 Vac
Poles	2
Trip Function	LIG
Continuous Current Rated	Standard
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Ground Fault	Yes
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

Classifications

UL File #	E51075
-----------	--------


by ABB

Publications

Title	Publication No.	Publication Type
Section 1 BuyLog: Load centers and circuit breakers	DET1023	Application and Technical
Guide includes product features, photos, product number selection guide, knockout drawings, wiring diagrams, accessories and options list. Only available on-line.		

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.