

Mico Pro electronic circuit protection, 1 channel

IN: 24 V DC OUT: 24 V DC / 4 A CL2

Art.No.: 9000-41011-0400001
Weight: 0.056
Country of origin: CZ
Model designation: Mico Pro fix 1.4 CL2


Mico Pro® fix 1.4
1 channel
Current adjustment 4 A
Build your own Mico Pro® online:
[START](#)

Link to Product

Illustration



Product may differ from Image



Header

Material short text Mico Pro fix 1.4 CL2

Commercial data

URL Webshop	https://shop.murrelektronik.com/9000-41011-0400001
GTIN	4048879772761
ECLASS-6.0	27371802
ECLASS-6.1	27371802
ECLASS-7.0	27371802
ECLASS-7.1	27371802
ECLASS-8.0	27371802
ECLASS-8.1	27371802
ECLASS-9.0	27371802
ECLASS-9.1	27371802
ECLASS-10.0.1	27371802
ECLASS-10.1	27371802
ECLASS-11.0	27371802
ECLASS-11.1	27371802

ECLASS-12.0	27371802
ECLASS-13.0	27371802
ECLASS-14.0	27371802
ETIM-5.0	EC001440
ETIM-6.0	EC001440
ETIM-7.0	EC001440
ETIM-8.0	EC001440
customs tariff number	85363030
EAN	4048879772761
Packaging unit	1

Electrical data | Supply

Total current max.	40 A
--------------------	------

Electrical data | Input

Input voltage DC min.	9 V
Input voltage DC max.	30 V
Input voltage 1 DC	12 V
Input voltage 2 DC	24 V
Total current bridge set max.	40 A
Control options	via power module
System supply	via power module

Electrical data | Output

Number of output channels	1
Triggering current DC full load per channel	3 A
Tolerance trigger current min.	0 %
Tolerance trigger current max.	9 %
Switch-on capacity max.	30 mF

Installation

Connection cross-section static min.	0.2 mm ²
Connection cross section static max.	2.5 mm ²
Connection cross-section dynamic min.	0.2 mm ²
Connection cross section dynamic max.	4 mm ²
AWG number static min.	14
AWG number static max.	24
AWG number dynamic min.	12
AWG number dynamic max.	24

Installation | Connection

Connection	Bridge system
------------	---------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Mounting data

Height	130 mm
Width	8 mm
Depth	114 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	55 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C

Connection type 6

Family construction form	Bridging Contact
No. of poles	1
Gender	female
Color contact carrier	black
PIN 1	UB +
Family construction form	Bridging Contact
No. of poles	1
Gender	female
Color contact carrier	black
PIN 1	0 V
Family construction form	Bridging Contact
No. of poles	4
Gender	female
Color contact carrier	black
PIN 1	On
PIN 2	Ctrl
PIN 3	Alarm
PIN 4	0.9
Family construction form	Bridging Contact
No. of poles	4
Gender	male
Color contact carrier	black
PIN 1	On
PIN 2	Ctrl
PIN 3	Alarm
PIN 4	0.9
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	0 V 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	Out 1