



Representative Image

Catalog No. TM3210CCU**Description: 100A 32CT 1P3W 120/240V 22K IC COMB****UPC No 783164114621****Home > Load Centers > Load Centers**

PowerMark Gold main breaker load centers arrive with a main breaker installed for a convenient and swift install. Main breakers allow for the user to stop the flow of electricity in the load center, shutting off all the power in the residence. The TM3210CCU features spaces for 32, 1" breakers, a 100 A bus ampere rating, a copper bus, and a combination/flush enclosure.

Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Specifications

Load Center Type	Standard
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	22
Amperage	100 A
Device type	Main Breaker
Enclosure	Indoor
Phase	1 Phase
1" Space	32
1/2" Space	0
Feed	Either
Door	Yes
GSA Compliance	Yes
Circuit Breaker Style	Plug-In
NEMA Rating	NEMA 1
Factory Installed Ground Kit	No
Enclosure Type	Indoor, Combination
Wires	3 Wire
Service & Voltage	1 Phase, 3 Wire, 120/240V ac

Classifications

UL/CUL Listing	UL
----------------	----


by ABB

Publications

Title	Publication No.	Publication Type
Section 1 BuyLog: Load centers and circuit breakers	DET1023	Application and Technical
Guide includes product features, photos, product number selection guide, knockout drawings, wiring diagrams, accessories and options list. Only available on-line.		

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.