

MICO+ 4.6 electronic circuit protection, 4 CHANNELS

IN: 24 V DC OUT: 24 V DC / 1-2-4-6 A

Art.No.: 9000-41084-0100600

Weight: 0.16



Country of origin: CZ

Model designation: MICO+ 4.6

MICO+ 4.6

4 channels

Current adjustment 1, 2, 4, 6 A

Link to Product
Illustration


Product may differ from Image


Header

Material short text

MICO+ 4.6

Commercial data

URL Webshop

<https://shop.murrelektronik.com/9000-41084-0100600>

GTIN	4048879328937
ECLASS-6.0	27371802
ECLASS-6.1	27371802
ECLASS-7.0	27371802
ECLASS-7.1	27371802
ECLASS-8.0	27371802
ECLASS-8.1	27371802
ECLASS-9.0	27371802
ECLASS-9.1	27371802
ECLASS-10.0.1	27371802
ECLASS-10.1	27371802
ECLASS-11.0	27371802
ECLASS-11.1	27371802
ECLASS-12.0	27371802
ECLASS-13.0	27371802
ECLASS-14.0	27371802
ETIM-5.0	EC001440
ETIM-6.0	EC001440
ETIM-7.0	EC001440
ETIM-8.0	EC001440
customs tariff number	85363010
EAN	4048879328937
Packaging unit	1
Electrical data Input	
Input voltage DC	24 V
Input voltage DC min.	18 V
Input voltage DC max.	30 V
Total current bridge set max.	40 A
ON input voltage control inputs min.	10 V
ON input voltage control inputs max.	30 V
ON pulse length control inputs high min.	20 ms
Electrical data Output	
Switch-on capacity per channel max.	20 mF
Switching current max.	20 mA
Installation	
Connection cross-section inputs max.	16 mm ²
Connection cross-section outputs max.	1.5 mm ²
Connection cross-section control inputs / control outputs max.	2.5 mm ²
Mechanical data Mounting data	
Height	90 mm
Width	70 mm
Depth	80 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C
Connection type 10	
Family construction form	Bridging Contact

No. of poles	1
Gender	female
Color contact carrier	black
PIN 1	24 V DC
Family construction form	Bridging Contact
No. of poles	1
Gender	female
Color contact carrier	black
PIN 1	0 V
Family construction form	Bridging Contact
No. of poles	2
Gender	female
Color contact carrier	black
PIN 1	On
PIN 2	Off
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	0 V
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	24 V DC
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	Out 1
PIN 2	Out 1
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	Out 2
PIN 2	Out 2
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	Out 3
PIN 2	Out 3
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	Out 4

PIN 2	Out 4
Family construction form	terminal
No. of poles	4
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	On
PIN 2	Off
PIN 3	14
PIN 4	0.9