



Catalog No. TY28MX-A

Description: CABLE TIE 50LB 14IN

UPC No 786209999085

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Heat Stabilized, Ultraviolet Resistant Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F) for Indoor or Outdoor Applications, UL/EN/CSA62275 Type 21S Rated, Length of 360.68mm (14.2 Inches), Width of 4.8mm (0.19 Inch), Thickness of 1.27mm (0.05 Inch), Tensile Strength Rating of 222 Newtons (50 pounds), Bulk Pack

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	49.9 pounds , 222 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405 UL E49405

Dimensions

Width	0.19 in , 4.7 mm
Length	14.2 in , 360 mm
Thickness	0.05 in , 1.3 mm
Bundle Diameter	0.31 to 3.74 in , 8 to 95 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	4.7 mm
Length belt/tape/tie	360 mm
Length belt/tape/tie	14.2 inch
Tie thickness	1.3 mm
Tie thickness	0.05 inch
Max. bundle diameter	95 mm
Min. holding force	222 N
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y