

Connectivity Solutions





Table of Contents

M12 Cordsets	4
M12 PUR Cordsets	10
M12 Specialty Cordsets	11
M12 Splitters and Tees	15
Molded I/O Junction Blocks	20
I/O Junction Blocks	22
M12 Power Cordsets	24
M12 Power Junction Blocks	25
M23 Cordsets	26
M8 Cordsets	30
Field Wireable Connectors	34

M12 PVC Cordsets





Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Vibration Shock: Meets IEC 60068-2-6 requirements

Mechanical Shock: Meets IEC 60068-2-27 requirements

Temperature: -40° to +70 °C

Environmental Rating: IP66, IP67, IP68, NEMA 1, UL Type 1



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Length	Straight	Right-Angle	Pinout
4-Pin Female QD to Flying Leads	1 m	BC-M12F4-22-1	BC-M12F4A-22-1	22 AWG Cable ø – 5.2 mm
	2 m	BC-M12F4-22-2	BC-M12F4A-22-2	
	5 m	BC-M12F4-22-5	BC-M12F4A-22-5	
	8 m	BC-M12F4-22-8	BC-M12F4A-22-8	
	10 m	BC-M12F4-22-10	BC-M12F4A-22-10	
	15 m	BC-M12F4-22-15	BC-M12F4A-22-15	



	Length	Straight	Right-Angle	Pinout
4-Pin Male QD to Flying Leads	1 m	BC-M12M4-22-1	—	22 AWG Cable ø – 5.2 mm
	2 m	BC-M12M4-22-2	—	
	5 m	BC-M12M4-22-5	—	
	8 m	BC-M12M4-22-8	—	
	10 m	BC-M12M4-22-10	—	



	Length	Straight/Straight (Female/Male)	Straight/Right-Angle (Female/Male)	Pinout
4-Pin Double-Ended	0.3 m	BC-M12F4-M12M4-22-0.3	BC-M12F4-M12M4A-22-0.3	22 AWG Cable ø – 5.2 mm
	0.5 m	BC-M12F4-M12M4-22-0.5	—	
	1 m	BC-M12F4-M12M4-22-1	BC-M12F4-M12M4A-22-1	
	2 m	BC-M12F4-M12M4-22-2	BC-M12F4-M12M4A-22-2	
	3 m	BC-M12F4-M12M4-22-3	—	
	4 m	BC-M12F4-M12M4-22-4	—	
	5 m	BC-M12F4-M12M4-22-5	BC-M12F4-M12M4A-22-5	
	6 m	BC-M12F4-M12M4-22-6	—	
	10 m	BC-M12F4-M12M4-22-10	BC-M12F4-M12M4A-22-10	
	15 m	BC-M12F4-M12M4-22-15	BC-M12F4-M12M4A-22-15	



	Length	Straight	Right-Angle	Pinout
4-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	BC-M12F4-22-2-SF	BC-M12F4A-22-2-SF	22 AWG Cable ø – 5.2 mm
	5 m	BC-M12F4-22-5-SF	—	
	10 m	BC-M12F4-22-10-SF	BC-M12F4A-22-10-SF	


*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M12 PVC Cordsets




5-Pin (Voltage: 60 V DC/AC, Current: 4 A)





	Length	Straight	Right-Angle	Pinout
5-Pin Female QD to Flying Leads	1 m	BC-M12F5-22-1	BC-M12F5A-22-1	 Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
	2 m	BC-M12F5-22-2	BC-M12F5A-22-2	
	5 m	BC-M12F5-22-5	BC-M12F5A-22-5	
	8 m	BC-M12F5-22-8	BC-M12F5A-22-8	
	10 m	BC-M12F5-22-10	BC-M12F5A-22-10	
	15 m	BC-M12F5-22-15	—	22 AWG Cable ø – 5.6 mm




5-Pin Male QD to Flying Leads	1 m	BC-M12M5-22-1	—	 Male 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
	2 m	BC-M12M5-22-2	—	
	5 m	BC-M12M5-22-5	—	
	8 m	BC-M12M5-22-8	—	
	10 m	BC-M12M5-22-10	—	
				22 AWG Cable ø – 5.6 mm



	Length	Straight/Straight (Female/Male)	Straight/Right-Angle	Pinout
5-Pin Double-Ended	1 m	BC-M12F5-M12M5-22-1	—	 Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray  Male 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
	2 m	BC-M12F5-M12M5-22-2	—	
	5 m	BC-M12F5-M12M5-22-5	—	
	8 m	BC-M12F5-M12M5-22-8	—	
	10 m	BC-M12F5-M12M5-22-10	—	
				22 AWG Cable ø – 5.6 mm



	Length	Straight	Right-Angle	Pinout
5-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	BC-M12F5-22-2-SF	BC-M12F5A-22-2-SF	 Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
	5 m	BC-M12F5-22-5-SF	BC-M12F5A-22-5-SF	
	9 m	BC-M12F5-22-10-SF	BC-M12F5A-22-10-SF	
	15 m	BC-M12F5-22-15-SF	—	
				22 AWG Cable ø – 5.7 mm


*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M12 PVC Cordsets





8-Pin (Voltage: 30 V DC/AC, Current: 2 A)



	Length	Straight	Right-Angle		Pinout	
8-Pin Female to Flying Leads	1 m	BC-M12F8-24-1	—		1 = White	5 = Gray
	2 m	BC-M12F8-24-2	—		2 = Brown	6 = Pink
	5 m	BC-M12F8-24-5	—		3 = Green	7 = Blue
	10 m	BC-M12F8-24-10	—		4 = Yellow	8 = Red
					Cable ø – 5.9 mm	

8-Pin Male to Flying Leads	1 m	BC-M12M8-24-1	—		1 = White	5 = Gray
	2 m	BC-M12M8-24-2	—		2 = Brown	6 = Pink
	5 m	BC-M12M8-24-5	—		3 = Green	7 = Blue
	10 m	BC-M12M8-24-10	—		4 = Yellow	8 = Red
					Cable ø – 5.9 mm	


	Length	Straight/Straight (Female/Male)	Right-Angle/Straight		Pinout
8-Pin Double-Ended	1 m	BC-M12F8-M12M8-24-1	—	 Female Male 24 AWG	1 = White 5 = Gray
	2 m	BC-M12F8-M12M8-24-2	—		2 = Brown 6 = Pink
	5 m	BC-M12F8-M12M8-24-5	—		3 = Green 7 = Blue
	8 m	BC-M12F8-M12M8-24-8	—		4 = Yellow 8 = Red
	10 m	BC-M12F8-M12M8-24-10	—		Cable ø – 5.9 mm


	Length	Straight	Right-Angle		Pinout
8-Pin Female QD to Flying Leads Open Shield with Drain Wire	1 m	BC-M12F8-24-1-SF	—	 Female 24 AWG	1 = White 5 = Gray
	2 m	BC-M12F8-24-2-SF	BC-M12F8A-24-2-SF		2 = Brown 6 = Pink
	5 m	BC-M12F8-24-5-SF	BC-M12F8A-24-5-SF		3 = Green 7 = Blue
	10 m	BC-M12F8-24-10-SF	BC-M12F8A-24-10-SF		4 = Yellow 8 = Red
	15 m	BC-M12F8-24-15-SF	—		Cable ø – 5.6 mm



12-Pin (Voltage: 30 V DC/AC, Current: 2 A)



	Length	Straight	Right-Angle		Pinout
12-Pin Female to Flying Leads	2 m	BC-M12F12-24-2	BC-M12F12A-24-2	 Female 24 AWG	1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Blue 8 = Red 9 = Orange 10 = Tan 11 = Black 12 = Violet
	5 m	BC-M12F12-24-5	BC-M12F12A-24-5		
	10 m	BC-M12F12-24-10	BC-M12F12A-24-10		

	Length	Straight/Straight (Female/Male)	Pinout			
12-Pin Double-Ended	2 m	BC-M12F12-M12M12-24-2			1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink	7 = Blue 8 = Red 9 = Orange 10 = Tan 11 = Black 12 = Violet
	5 m	BC-M12F12-M12M12-24-5				
	10 m	BC-M12F12-M12M12-24-10				
			24 AWG		Cable ø – 6.4 mm	

*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

Legacy M12 PVC Cordsets





Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Vibration Shock: Meets IEC 60068-2-6 requirements

Mechanical Shock: Meets IEC 60068-2-27 requirements


Temperature: -40° to +70 °C

Environmental Rating: IP66, IP67, IP68, NEMA 1, UL Type 1




4-Pin (Voltage: 250 V DC/AC, Current: 4 A)





	Length	Straight	Right-Angle	Pinout
4-Pin Female QD to Flying Leads	1 m	MQDC-403	—	 Female 1 = Brown 2 = White 3 = Blue 4 = Black
	2 m	MQDC-406	MQDC-406RA	
	3 m	MQDC-410	—	
	5 m	MQDC-415	MQDC-415RA	
	9 m	MQDC-430	MQDC-430RA	
	15 m	MQDC-450	MQDC-450RA	
	18 m	MQDC-460	MQDC-460RA	
	21 m	MQDC-470	MQDC-470RA	
	30 m	MQDC-4100	MQDC-4100RA	
				22 AWG Cable ø – 5.2 mm




	Length	Straight	Right-Angle	Pinout
4-Pin Male QD to Flying Leads	2 m	MQDMC-406	MQDMC-406RA	 Male 1 = Brown 2 = White 3 = Blue 4 = Black
	5 m	MQDMC-415	MQDMC-415RA	
	9 m	MQDMC-430	MQDMC-430RA	
				22 AWG Cable ø – 5.2 mm



	Length	Straight/Straight (Female/Male)	Straight/Right-Angle (Female/Male)	Pinout
4-Pin Double-Ended	0.3 m	MQDEC-401SS	MQDEC-401RS	 Female 1 = Brown 2 = White 3 = Blue 4 = Black
	0.6 m	MQDEC-402SS	—	
	0.9 m	MQDEC-403SS	MQDEC-403RS	
	1.8 m	MQDEC-406SS	MQDEC-406RS	
	3.0 m	MQDEC-410SS	—	
	3.6 m	MQDEC-412SS	MQDEC-412RS	 Male 1 = Brown 2 = White 3 = Blue 4 = Black
	4.5 m	MQDEC-415SS	—	
	6.1 m	MQDEC-420SS	MQDEC-420RS	
	9.2 m	MQDEC-430SS	MQDEC-430RS	
	15.2 m	MQDEC-450SS	MQDEC-450RS	
				22 AWG Cable ø – 5.2 mm




	Length	Straight	Right-Angle	Pinout
4-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	MQDEC2-406	MQDEC2-406RA	 Female 1 = Brown 2 = White 3 = Blue 4 = Black
	5 m	MQDEC2-415	MQDEC2-415RA	
	9 m	MQDEC2-430	MQDEC2-430RA	
	15 m	MQDEC2-450	MQDEC2-450RA	
				22 AWG Cable ø – 5.2 mm

*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.


Legacy M12 PVC Cordsets

5-Pin (Voltage: 60 V DC/AC, Current: 4 A)




	Length	Straight	Right-Angle	Pinout
5-Pin Female QD to Flying Leads	0.9 m	MQDC1-503	—	 Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
	2 m	MQDC1-506	MQDC1-506RA	
	5 m	MQDC1-515	MQDC1-515RA	
	9 m	MQDC1-530	MQDC1-530RA	
	18 m	MQDC1-560	—	
	30 m	MQDC1-5100	—	
				22 AWG Cable ø – 5.6 mm




5-Pin Male QD to Flying Leads	2 m	MQDMC-506	MQDMC-506RA	 Male 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
	5 m	MQDMC-515	MQDMC-515RA	
	9 m	MQDMC-530	MQDMC-530RA	
				22 AWG Cable ø – 5.6 mm



	Length	Straight/Straight (Female/Male)	Straight/Right-Angle	Pinout
5-Pin Double-Ended	0.3 m	MQDEC-501SS	—	 Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
	1 m	MQDEC-503SS	—	
	2 m	MQDEC-506SS	—	
	5 m	MQDEC-515SS	—	
	9 m	MQDEC-530SS	—	
	15 m	MQDEC-550SS	—	
				22 AWG Cable ø – 5.6 mm




	Length	Straight	Right-Angle	Pinout
5-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	MQDEC2-506	MQDEC2-506RA	 Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
	5 m	MQDEC2-515	MQDEC2-515RA	
	9 m	MQDEC2-530	MQDEC2-530RA	
	15 m	MQDEC2-550	MQDEC2-550RA	
	23 m	MQDEC2-575	MQDEC2-575RA	
	30 m	MQDEC2-5100	MQDEC2-5100RA	
				22 AWG Cable ø – 5.7 mm

*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.


Legacy M12 PVC Cordsets

8-Pin (Voltage: 30 V DC/AC, Current: 2 A)



	Length	Straight	Right-Angle		Pinout
8-Pin Female to Flying Leads	2 m	MQDC1-806	MQDC1-806RA		1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red
	5 m	MQDC1-815	MQDC1-815RA		
	9 m	MQDC1-830	MQDC1-830RA		
	15 m	MQDC1-850	MQDC1-850RA		
	30 m	MQDC1-8100	—		
				24 AWG	Cable ø – 5.9 mm




8-Pin Male to Flying Leads	2 m	MQDMC1-806	—		1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red
	5 m	MQDMC1-815	—		
	9 m	MQDMC1-830	—		
	15 m	MQDMC1-850	—		
				24 AWG	Cable ø – 5.9 mm




	Length	Straight/Straight (Female/Male)	Right-Angle/Straight	Pinout	
8-Pin Double-Ended	1 m	MQDEC1-803SS	—		1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red
	2 m	MQDEC1-806SS	—		
	5 m	MQDEC1-815SS	—		
	9 m	MQDEC1-830SS	—		
	15 m	MQDEC1-850SS	—		
	30 m	MQDEC1-8100SS	—		
				24 AWG	Cable ø – 5.9 mm



	Length	Straight	Right-Angle		Pinout
8-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	MQDC2S-806	MQDC2S-806RA		1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red
	5 m	MQDC2S-815	MQDC2S-815RA		
	10 m	MQDC2S-830	MQDC2S-830RA		
	16 m	MQDC2S-850	MQDC2S-850RA		
	31 m	MQDC2S-8100	—		
				24 AWG	Cable ø – 5.6 mm

12-Pin (Voltage: 30 V DC/AC, Current: 2 A)



	Length	Straight	Right-Angle		Pinout
12-Pin Female to Flying Leads	2 m	MQDC-1206	—		1 = White 7 = Blue 2 = Brown 8 = Red 3 = Green 9 = Orange 4 = Yellow 10 = Tan 5 = Gray 11 = Black 6 = Pink 12 = Violet
	3 m	MQDC-1210	—		
	5 m	MQDC-1215	—		
	9 m	MQDC-1230	—		
				24 AWG	Cable ø – 6.35 mm

*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M12 PUR Cordsets





Cable: PUR jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Vibration Shock: Meets IEC 60068-2-6 requirements

Mechanical Shock: Meets IEC 60068-2-27 requirements


Temperature: -40° to +70 °C

Environmental Rating: IP66, IP67, IP68, NEMA 1, UL Type 1





4-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Length	Straight	Right-Angle	Pinout
4-Pin Female QD to Flying Leads	2 m	MQDC-406-PUR	MQDC-406RA-PUR	 Female 1 = Brown 2 = White 3 = Blue 4 = Black 22 AWG Cable ø – 4.1 mm
	5 m	MQDC-415-PUR	MQDC-415RA-PUR	
	10 m	MQDC-430-PUR	MQDC-430RA-PUR	



	Length	Straight/Straight (Female/Male)	Right-Angle/Straight (Female/Male)	Pinout
4-Pin Double-Ended	0.3 m	MQDEC-401SS-PUR	MQDEC-401SR-PUR	 Female 1 = Brown 2 = White 3 = Blue 4 = Black
	0.6 m	MQDEC-402SS-PUR	MQDEC-402SR-PUR	
	1 m	MQDEC-403SS-PUR	MQDEC-403SR-PUR	
	2 m	MQDEC-406SS-PUR	MQDEC-406SR-PUR	 Male 1 = Brown 2 = White 3 = Blue 4 = Black 22 AWG Cable ø – 4.1 mm
	3 m	MQDEC-409SS-PUR	MQDEC-409SR-PUR	
	5 m	MQDEC-415SS-PUR	MQDEC-415SR-PUR	
	10 m	MQDEC-430SS-PUR	MQDEC-430SR-PUR	

*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M12 Specialty Cordsets

Lighted Cordsets

Cable: PVC jacket, translucent white PVC connector body, nickel-plated brass coupling nut





Vibration Shock: Meets IEC 60068-2-6 requirements

Mechanical Shock: Meets IEC 60068-2-27 requirements

Temperature: Max current of 1.0 A: -40 to +60 °C
Max current of 2.0 A: -40 to +55 °C
Max current of 4.0 A: -40 to +45 °C

Environmental Rating: IP66, IP67, IP68, NEMA 1, UL Type 1

LED Operation: Green LED indicates power ON; Yellow LED overrides green LED when pin 4 is active



4-Pin (Voltage: 10 to 30 V DC at 15 mA max)

	Length	Straight	Right-Angle	Pinout
4-Pin PNP	2 m	MQDC-406-GYP	MQDC-406-GYPRA	Female 1 = Brown 2 = White 3 = Blue 4 = Black (output LED) 22 AWG Cable ø – 5.2 mm
	5 m	MQDC-415-GYP	MQDC-415-GYPRA	
	9 m	MQDC-430-GYP	MQDC-430-GYPRA	
4-Pin NPN	2 m	MQDC-406-GYN	MQDC-406-GYNRA	Female 1 = Brown 2 = White 3 = Blue 4 = Black (output LED) 22 AWG Cable ø – 5.2 mm
	5 m	MQDC-415-GYN	MQDC-415-GYNRA	
	9 m	MQDC-430-GYN	MQDC-430-GYNRA	


5-Pin (Voltage: 10 to 30 V DC at 15 mA max)

	Length	Straight	Right-Angle	Pinout
5-Pin PNP	2 m	MQDC-506-GYP	MQDC-506-GYPRA	Female 1 = Brown 2 = White 3 = Blue 4 = Black (output LED) 5 = Gray 22 AWG Cable ø – 5.6 mm
	5 m	MQDC-515-GYP	MQDC-515-GYPRA	
	9 m	MQDC-530-GYP	MQDC-530-GYPRA	
5-Pin NPN	2 m	MQDC-506-GYN	MQDC-506-GYNRA	Female 1 = Brown 2 = White 3 = Blue 4 = Black (output LED) 5 = Gray 22 AWG Cable ø – 5.6 mm
	5 m	MQDC-515-GYN	MQDC-515-GYNRA	
	9 m	MQDC-530-GYN	MQDC-530-GYNRA	

M12 Specialty Cordsets

Coiled Cordsets

- Cable:** PUR jacket, black PUR connector body, nickel-plated brass coupling nut
- Vibration Shock:** Meets IEC 60068-2-6 requirements
- Mechanical Shock:** Meets IEC 60068-2-27 requirements
- Temperature:** -40° to +70 °C
- Environmental Rating:** IP67, IP69K, NEMA 1, 3, 4, 6P, 13



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)



4-Pin	Length (retracted to extended)	Straight	Pinout	
	0.8 to 1.7 m	MQDC-401.7M-PUR-C		1 = Brown 2 = White 3 = Blue 4 = Black
	1.0 to 2.6 m	MQDC-402.6M-PUR-C		
	1.2 to 3.3 m	MQDC-403.3M-PUR-C		
			22 AWG	Cable ø – 5.2 mm



4-Pin Double-Ended	Length (retracted to extended)	Straight/Straight	Pinout	
	0.8 to 1.7 m	MQDEC-401.7M-PUR-C		1 = Brown 2 = White 3 = Blue 4 = Black
	1.0 to 2.6 m	MQDEC-403.3M-PUR-C		
			22 AWG	Cable ø – 5.2 mm

M12 Specialty Cordsets

High Pressure and Temperature Washdown Cordsets

Cable: PVC jacket, 316 stainless steel nut


Vibration Shock: Meets IEC 60068-2-6 requirements

Mechanical Shock: Meets IEC 60068-2-27 requirements

Temperature: -40 to +70 °C


Environmental Rating: IP66, IP67, IP68, IP69K, NEMA 1, UL Type 1

Certifications: **ECOLAB** test F and E Nr. 40-1




4-Pin (Voltage: 250 V DC/AC, Current: 4 A)




	Length	Straight	Pinout
4-Pin	2 m	MQDC-WDSS-0406	
	5 m	MQDC-WDSS-0415	
	9 m	MQDC-WDSS-0430	




	Length	Straight/Straight	Pinout
4-Pin Double-Ended	0.31 m	MQDEC-WDSS-401SS	
	0.91 m	MQDEC-WDSS-403SS	
	1.83 m	MQDEC-WDSS-406SS	
	3.7 m	MQDEC-WDSS-412SS	

5-Pin (Voltage: 60 V DC/AC, Current: 4 A)



	Length	Straight	Pinout
5-Pin	2 m	MQDC-WDSS-0506	
	5 m	MQDC-WDSS-0515	
	9 m	MQDC-WDSS-0530	



	Length	Straight/Straight	Pinout
5-Pin Double-Ended	1.5 m	MQDEC-WDSS-505SS	
	3 m	MQDEC-WDSS-510SS	
	4.57 m	MQDEC-WDSS-515SS	

M12 Specialty Cordsets

Chemical Washdown Cordsets


Cable: White polypropylene jacket, polypropylene connector body, polypropylene contact carriers, 316 stainless steel nut

Vibration Shock: Meets IEC 60068-2-6 requirements

Mechanical Shock: Meets IEC 60068-2-27 requirements

Temperature: -40 °C to +90 °C

Environmental Rating: IP68, NEMA 1, 3, 4, 6P



5-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Length	Straight	Pinout
5-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	MQDCWD-506	Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray 22 AWG Cable ø – 4.5 mm
	9 m	MQDCWD-530	

Namur


Cable: Blue PVC jacket, PUR connector body, nickel-plated brass coupling nut

Vibration Shock: Meets IEC 60068-2-6 requirements


Mechanical Shock: Meets IEC 60068-2-27 requirements

Temperature: -40 °C to +105 °C

Environmental Rating: IP67, NEMA 1, 3, 4, 6P, 13



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Length	Straight	Right-Angle	Pinout
4-Pin	2 m	MQD9-406	MQD9-406RA	Female 1 = Brown 2 = Blue 20 AWG Cable ø – 5.2 mm
	5 m	MQD9-415	MQD9-415RA	
	9 m	MQD9-430	MQD9-430RA	


M12 Splitters and Tees

Round QD Splitters


Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Temperature: -40 to +90 °C


Environmental Rating: IP68




Example of Parallel 4-Pin Wiring



S15YA24-M124-M124-0.2M
Non-parallel 4-Pin Wiring





S15YA4-M124-M124-0.2M
Non-parallel 4-Pin Wiring





4-Pin (Voltage: 60 V DC/AC, Current: 2 A)



	Models	Cable Lengths		Pinout
		Trunk (Male)	Branches (Female)	
4-Pin	CSRB-M1240M1241	No Trunk/ Integral QD	0.3 m	 Female 1 = Brown 2 = White 3 = Blue 4 = Black
	CSRB-M1240M1242		0.6 m	
	CSRB-M1240M1243		0.9 m	
	CSRB-M1240M1244		1.2 m	
4-Pin	S15YA24-M124-M124-0.2M	No Trunk/ Integral QD	0.2 m	 Male 4 x 22 AWG Cable ø – 5.5 mm
	S15YA4-M124-M124-0.2M			
	S15YB-M124-M124-0.2M			

5-Pin (Voltage: 60 V DC/AC, Current: 2 A)



	Models	Cable Lengths		Pinout
		Trunk (Male)	Branches (Female)	
5-Pin	CSRB-M1250M125.47M125.73	No Trunk/ Integral QD	Branch 1 0.14 m Branch 2 0.22 m	 Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gn/Ye  Male 5 x 22 AWG Cable ø – 5.5 mm

M12 Splitters and Tees





Compact Flat QD Splitters and Tees

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Temperature: -40 to +90 °C

Environmental Rating: IP68

Example of Parallel 4-Pin Wiring



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Models	Dimensional Drawing	Pinout
4-Pin	CSB-M1240M1240	Figure A	Female 1 = Brown 2 = White 3 = Blue 4 = Black Male 22 AWG Cable ø – 6.0 mm

5-Pin (Voltage: 30 V DC/AC, Current: 2 A)



	Models	Dimensional Drawing	Pinout
5-Pin	CSB-M1250M1250-T	Figure C	Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray Male 22 AWG Cable ø – 5.5 mm
	CSB-M1250M1250A	Figure A	
	CSB-M1250M1250	Figure B	

8-Pin (Voltage: 60 V DC/AC, Current: 2 A)



	Models	Dimensional Drawing	Pinout
8-Pin	CSB-M1280M1280	Figure A	Female 1 = Brown 2 = Or/Bk 3 = Orange 4 = White 5 = Black 6 = Blue 7 = Gr/Ye 8 = Violet Male 22 AWG Cable ø – 6.0 mm

M12 Splitters and Tees




Flat QD Splitters

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Temperature: -40 to +90 °C

Environmental Rating: IP68

Example of Parallel 4-Pin Wiring



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)



	Models	Cable Lengths		Pinout
		Trunk (Male)	Branches (Female)	
4-Pin	CSB-M1240M1241	No Trunk/Integral QD	2 x 0.3 m	Female Male 22 AWG Cable ø – 6.0 mm
	CSB-M1241M1241	0.3 m	2 x 0.3 m	
	CSB-M1243M1243	1 m	2 x 1 m	
	CSB-M1248M1241	2.4 m	2 x 0.3 m	
	CSB-M12415M1241	4.6 m	2 x 0.3 m	
	CSB-UNT425M1241	7.6 m Unterminated	2 x 0.3 m	

5-Pin (Voltage: 30 V DC/AC, Current: 2 A)



	Models	Cable Lengths		Pinout
		Trunk	Branches	
5-Pin	CSB-M1251M1251B	0.3 m (Male)	2 x 0.3 m (Female)	Female Male 22 AWG Cable ø – 5.9 mm
	CSB-M1251FM1251M	0.3 m (Female)	2 x 0.3 m (Male)	

8-Pin (Voltage: 60 V DC/AC, Current: 2 A)



	Models	Cable Lengths		Pinout
		Trunk (Male)	Branches (Female)	
8-Pin	CSB-M1281M1281B	0.3 m	2 x 0.3 m	Female Male 22 AWG Cable ø – 6.0 mm

M12 Splitters and Tees




Wiring Splitters

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut



Temperature: -40 to +105 °C

Environmental Rating: IP68

Example of 4-Pin Wiring



4-Pin (Voltage: 250 V DC/AC, Current: 4 A)

	Models	Cable Lengths		Pinout
		Trunk (Male)	Branches (Female)	
 4-Pin	CSA-M1240M1241	No Trunk/ Integral QD	2 x 0.3 m	 Female  Male 1 = Brown 2 = White 3 = Blue 4 = Black
	CSA-M1240M1243	No Trunk/ Integral QD	2 x 1 m	
	CSA-M1240M1246	No Trunk/ Integral QD	2 x 2 m	
	CSA-M1241M1241	0.3 m	2 x 0.3 m	
	CSA-M1243M1243	1 m	2 x 1 m	
	CSA-M1246M1246	2 m	2 x 2 m	
				22 AWG Cable ø – 6.0 mm


M12 Multi-port Splitters

Multi-port Splitters


Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Temperature: -40° to +90 °C

Environmental Rating: IP68



Example of Parallel 5-Pin Wiring
(diagram applies to all branches)





5-Pin (Voltage: 30 V DC/AC, Current: 2 A)




Models		Cable Lengths		Pinout
		Branches (Female)	Trunk (Male)	
5-Pin	CSB4-M1251M1250	4 x No Branch / Integral QD	0.3 m	Female Male 1 = Brown 2 = White 3 = Blue 4 = Black 4 x 22 AWG Cable ø – 5.6 mm

M12 Molded Junction Blocks

Temperature: -40 to +70 °C
Environmental Rating: IP65, IP67, and IP68




Example of Parallel 5-Pin Wiring
(diagram applies to all branches)



5-Pin (Voltage: 30 V DC/AC, Current: 2 A)




Models	Cable Lengths		Pinout
	Branches (Female)	Trunk (Male)	
5-Pin	R50-4M125-M125Q-P	4 x No Branch/ Integral QD	No Trunk/Integral QD
	R95-8M125-M125Q-P	8 x No Branch/ Integral QD	No Trunk/Integral QD




Molded I/O Junction Blocks

Temperature: -40 to +70 °C

Environmental Rating: IP67





Wiring Diagram



5-Pin (Voltage: 30 V DC/AC, Current: 2 A)




Models		Cable Lengths		Pinout
		Branches (Female)	Trunk	
5-Pin	R95-8M125-C1-D24P	8 x No Branch/ Integral QD	1 m with Flying Leads	 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
	R95-8M125-0.3M23-D24P		0.3 m 19-pin M23 Male QD	
	R95-8M125-C1-D24		1 m with Flying Leads	 1 = Purple 2 = Red 3 = Gray 4 = Red/Blue 5 = Green 6 = Blue (18 AWG) 7 = Gray/Pink 8 = White/Green 9 = White/Yellow 10 = White/Gray 11 = Black 12 = Green/Yellow (18 AWG) 13 = Yellow/Brown 14 = Brown/Green 15 = White 16 = Yellow 17 = Pink 18 = Gray/Brown 19 = Brown (18 AWG)
	R95-8M125-0.3M23-D24		0.3 m 19-pin M23 Male QD	
				18 and 22 AWG Cable Ø – 9.2 mm


M8 I/O Junction Blocks

Temperature: -25 to +80 °C

Environmental Rating: IP67




Wiring Diagram




4 Port 3-Pin (Voltage: 120 V DC/AC, Current: 2 A)

	Models	Output	Pinout
	JB-4M8-M12-P4	PNP	Female 1 = Brown 3 = Blue 4 = Black Male 1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red
	JB-4M8-M12-N4	NPN	
	JB-4M8-M12-4	Discrete	



Wiring Diagram




8 Port 3-Pin (Voltage: 120 V DC/AC, Current: 2 A)

	Models	Output	Pinout
	JB-8M8-M12-P4	PNP	Female 1 = Brown 3 = Blue 4 = Black Male 1 = White 7 = Blue 2 = Brown 8 = Red 3 = Green 9 = Orange 4 = Yellow 10 = Tyrian Purple 5 = Gray 11 = Black 6 = Pink 12 = Violet
	JB-8M8-M12-N4	NPN	
	JB-8M8-M12-4	Discrete	


M12 I/O Junction Blocks

Temperature: -25 to +80 °C

Environmental Rating: IP67




Wiring Diagram




4 Port 5-Pin (Voltage: 120 V DC/AC, Current: 2 A)



	Models	Output	Pinout
5-Pin to 12-Pin	JB-4M12-M23-P24	PNP	Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray Male 1 = White 7 = Blue 2 = Brown 8 = Red 3 = Green 9 = Orange 4 = Yellow 10 = Tyrian Purple 5 = Gray 11 = Black 6 = Pink 12 = Violet
	JB-4M12-M23-N24	NPN	
	JB-4M12-M23-24	Discrete	



Wiring Diagram



8 Port 5-Pin (Voltage: 120 V DC/AC, Current: 2 A)




	Models	Output	Pinout
5-Pin to 19-Pin	JB-8M12-M23-P24	PNP	Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray Male 1 = Purple 11 = Black 2 = Red 12 = Green/Yellow (18 AWG) 3 = Gray 13 = Yellow/Brown 4 = Red/Blue 14 = Brown/Green 5 = Green 15 = White 6 = Blue (18 AWG) 16 = Yellow 7 = Gray/Pink 17 = Pink 8 = White/Green 18 = Gray/Brown 9 = White/Yellow 19 = Brown (18 AWG) 10 = White/Gray
	JB-8M12-M23-N24	NPN	
	JB-8M12-M23-24	Discrete	

M12 Power Cordsets



Cable: Shielded PVC jacket with black TPU overmolding, nickel-plated brass coupling nut, gold-plated brass terminal

Temperature: Fixed installation: -40 °C to +85 °C , flexible installation: -25 °C to +85 °C

Environmental Rating: IP67, IP68




5-Pin L-Code (Voltage: 63 V DC/AC, Current: 16 A)

	Length	Straight	Pinout
 5-Pin Female QD to Flying Leads	1 m	BCP-M12LF5-14-1	 Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow/Green - Shell = Braid
	2 m	BCP-M12LF5-14-2	
	5 m	BCP-M12LF5-14-5	
	10 m	BCP-M12LF5-14-10	
	15 m	BCP-M12LF5-14-15	
	20 m	BCP-M12LF5-14-20	
 5-Pin Male QD to Flying Leads	1 m	BCP-M12LM5-14-1	 Male 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow/Green - Shell = Braid
	2 m	BCP-M12LM5-14-2	
	5 m	BCP-M12LM5-14-5	
	10 m	BCP-M12LM5-14-10	
	15 m	BCP-M12LM5-14-15	
	20 m	BCP-M12LM5-14-20	
	Length	Straight/Straight (Female/Male)	Pinout
 5-Pin Double-Ended	1 m	BCP-M12LF5-M12LM5-14-1	 Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow/Green - Shell = Braid Male 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow/Green - Shell = Braid
	2 m	BCP-M12LF5-M12LM5-14-2	
	5 m	BCP-M12LF5-M12LM5-14-5	
	10 m	BCP-M12LF5-M12LM5-14-10	
	15 m	BCP-M12LF5-M12LM5-14-15	
	20 m	BCP-M12LF5-M12LM5-14-20	


M12 Power Junction Blocks

Temperature: -40 °C to +70 °C

Environmental Rating: IP67



Example of Parallel Wiring





5-Pin L-Code (Voltage: 60 V DC, Current: 16 A)



Models	Connection	Pinout
R50-2M125L-M125-P	1 x L-code male M12 2 x L-code female M12	Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow/Green
R50T-2M125L-M125-P	1 x L-code male M12 2 x L-code female M12	Male 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow/Green

Temperature: -40 °C to +70 °C

Environmental Rating: IP65, IP67, IP68



5-Pin L-Code to A-Code (Voltage: 63 V DC, Current: 4 A A-Code, 16 A L-Code)




Model	Power Connections	Power Drops	Pinout
R50-M12LM5-M12LF5-2M12F5-P13	1 x L-code male M12 1 x L-code female M12	2 x A-code female M12	Female 1 = Brown 2 = NC 3 = Blue 4 = NC 5 = NC Male 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow/Green Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow/Green

M23 PVC Cordsets

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut


Temperature: -25° to +85 °C

Environmental Rating: IP67 and IP68




19-Pin (Voltage: 150 V DC/AC, Current: 8 A (18 gauge), 2A (22 gauge))



	Length	Straight	Pinout
19-Pin Female QD to Flying Leads	1 m	BC-M23F19-1822-1	Female  1 = Purple 2 = Red 3 = Gray 4 = Red/Blue 5 = Green 6 = Blue (18 AWG) 7 = Gray/Pink 8 = White/Green 9 = White/Yellow 10 = White/Gray 11 = Black 12 = Green/Yellow (18 AWG) 13 = Yellow/Brown 14 = Brown/Green 15 = White 16 = Yellow 17 = Pink 18 = Gray/Brown 19 = Brown (18 AWG)
	2 m	BC-M23F19-1822-2	
	5 m	BC-M23F19-1822-5	
	10 m	BC-M23F19-1822-10	
	15 m	BC-M23F19-1822-15	
	20 m	BC-M23F19-1822-20	
			18 and 22 AWG Cable ø – 9.8 mm



	Length	Straight	Pinout
19-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	BC-M23F19-1822-2-SFP	Female  1 = Purple 2 = Red 3 = Gray 4 = Red/Blue 5 = Green 6 = Blue (18 AWG) 7 = Gray/Pink 8 = White/Green 9 = White/Yellow 10 = White/Gray 11 = Black 12 = Green/Yellow (18 AWG) 13 = Yellow/Brown 14 = Brown/Green 15 = White 16 = Yellow 17 = Pink 18 = Gray/Brown 19 = Brown (18 AWG)
	5 m	BC-M23F19-1822-5-SFP	
	10 m	BC-M23F19-1822-10-SFP	
			18 and 22 AWG Cable ø – 9.8 mm


*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M23 PVC Cordsets

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut


Temperature: -25° to +85 °C

Environmental Rating: IP67 and IP68




19-Pin (Voltage: 150 V DC/AC, Current: 8 A (18 gauge), 2A (22 gauge))



	Length	Straight	Pinout
19-Pin Male QD to Flying Leads	1 m	BC-M23M19-1822-1	 Male 1 = Purple 2 = Red 3 = Gray 4 = Red/Blue 5 = Green 6 = Blue (18 AWG) 7 = Gray/Pink 8 = White/Green 9 = White/Yellow 10 = White/Gray 11 = Black 12 = Green/Yellow (18 AWG) 13 = Yellow/Brown 14 = Brown/Green 15 = White 16 = Yellow 17 = Pink 18 = Gray/Brown 19 = Brown (18 AWG)
	2 m	BC-M23M19-1822-2	
	5 m	BC-M23M19-1822-5	
	10 m	BC-M23M19-1822-10	
	15 m	BC-M23M19-1822-10	
	20 m	BC-M23M19-1822-20	
			18 and 22 AWG Cable ø – 9.8 mm



	Length	Straight/Straight (Female/Male)	Pinout
19-Pin Double-Ended	1 m	BC-M23F19-M23M19-1822-1	 Female 1 = Purple 2 = Red 3 = Gray 4 = Red/Blue 5 = Green 6 = Blue (18 AWG) 7 = Gray/Pink 8 = White/Green 9 = White/Yellow 10 = White/Gray 11 = Black 12 = Green/Yellow (18 AWG) 13 = Yellow/Brown 14 = Brown/Green 15 = White 16 = Yellow 17 = Pink 18 = Gray/Brown 19 = Brown (18 AWG)
	2 m	BC-M23F19-M23M19-1822-2	
	5 m	BC-M23F19-M23M19-1822-5	
	10 m	BC-M23F19-M23M19-1822-10	
	15 m	BC-M23F19-M23M19-1822-15	
	20 m	BC-M23F19-M23M19-1822-20	
			18 and 22 AWG Cable ø – 9.8 mm


*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M23 PVC Cordsets

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut


Temperature: -25° to +85 °C

Environmental Rating: IP67 and IP68




12-Pin (Voltage: 300 V DC/AC, Current: 4 A)




	Length	Straight	Right-Angle	Pinout
12-Pin Female QD to Flying Leads	1 m	BC-M23F12-22-1	—	 Female 1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Blue 8 = Red 9 = Orange 10 = Tyrian Purple 11 = Black 12 = Violet
	2 m	BC-M23F12-22-2	BC-M23F12A-22-2	
	5 m	BC-M23F12-22-5	BC-M23F12A-22-5	
	10 m	BC-M23F12-22-10	BC-M23F12A-22-10	
	15 m	BC-M23F12-22-15	—	
	20 m	BC-M23F12-22-20	—	
				22 AWG Cable ø – 6 mm



12-Pin Female QD to Flying Leads Open Shield with Drain Wire	2 m	BC-M23F12-22-2-SFP	BC-M23F12A-22-2-SFP	 Female 1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Blue 8 = Red 9 = Orange 10 = Tyrian Purple 11 = Black Cut = Violet 12 = Drain + Braid
	5 m	BC-M23F12-22-5-SFP	BC-M23F12A-22-5-SFP	
	10 m	BC-M23F12-22-10-SFP	BC-M23F12A-22-10-SFP	
				22 AWG Cable ø – 6 mm



12-Pin Male QD to Flying Leads	1 m	BC-M23M12-22-1	—	 Male 1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Blue 8 = Red 9 = Orange 10 = Tyrian Purple 11 = Black 12 = Violet
	2 m	BC-M23M12-22-2	—	
	5 m	BC-M23M12-22-5	—	
	10 m	BC-M23M12-22-10	—	
	15 m	BC-M23M12-22-15	—	
	20 m	BC-M23M12-22-20	—	
				22 AWG Cable ø – 9.8 mm


*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M23 PVC Cordsets

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut



Temperature: -25° to +85 °C

Environmental Rating: IP67 and IP68



12-Pin (Voltage: 300 V DC/AC, Current: 4 A)



	Length	Straight/Straight (Female/Male)	Pinout
12-Pin Double-Ended	2 m	BC-M23F12-M23M12-22-2	Female  Male  1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Blue 8 = Red 9 = Orange 10 = Tyrian Purple 11 = Black 12 = Violet
	5 m	BC-M23F12-M23M12-22-5	
	10 m	BC-M23F12-M23M12-22-10	
	15 m	BC-M23F12-M23M12-22-15	
	20 m	BC-M23F12-M23M12-22-20	
			22 AWG Cable ø – 6 mm


*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M8 PVC Cordsets

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Temperature: -40° to +70 °C

Environmental Rating: IP67



3-Pin (Voltage: 30 V DC, Current: 4 A)




	Length	Straight	Pinout	
3-Pin Female QD to Flying Leads	0.5 m	BC-M8F3-24-0.5		1 = Brown 3 = Blue 4 = Black
	1 m	BC-M8F3-24-1		
	2 m	BC-M8F3-24-2		
	5 m	BC-M8F3-24-5		
	8 m	BC-M8F3-24-8		
	10 m	BC-M8F3-24-10		
			24 AWG	Cable ø – 4.2 mm



3-Pin Male QD to Flying Leads	0.5 m	BC-M8M3-24-0.5		1 = Brown 3 = Blue 4 = Black
	1 m	BC-M8M3-24-1		
	2 m	BC-M8M3-24-2		
	5 m	BC-M8M3-24-5		
	8 m	BC-M8M3-24-8		
	10 m	BC-M8M3-24-10		
			24 AWG	Cable ø – 4.2 mm



	Length	Straight/Straight (Female/Male)	Pinout	
3-Pin Double-Ended	0.5 m	BC-M8F3-M8M3-24-0.5		1 = Brown 3 = Blue 4 = Black
	1 m	BC-M8F3-M8M3-24-1		
	2 m	BC-M8F3-M8M3-24-2		
	5 m	BC-M8F3-M8M3-24-5		
	8 m	BC-M8F3-M8M3-24-8		
	10 m	BC-M8F3-M8M3-24-10		
			24 AWG	Cable ø – 4.2 mm


*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M8 PVC Cordsets




4-Pin (Voltage: 30 V DC, Current: 4 A)




	Length	Straight	Pinout	
4-Pin Female QD to Flying Leads	0.5 m	BC-M8F4-24-0.5		1 = Brown 2 = White 3 = Blue 4 = Black
	1 m	BC-M8F4-24-1		
	2 m	BC-M8F4-24-2		
	5 m	BC-M8F4-24-5		
	8 m	BC-M8F4-24-8		
	10 m	BC-M8F4-24-10		
			24 AWG	Cable ø – 4.4 mm



4-Pin Male QD to Flying Leads	0.5 m	BC-M8M4-24-0.5		1 = Brown 2 = White 3 = Blue 4 = Black
	1 m	BC-M8M4-24-1		
	2 m	BC-M8M4-24-2		
	5 m	BC-M8M4-24-5		
	8 m	BC-M8M4-24-8		
	10 m	BC-M8M4-24-10		
			24 AWG	Cable ø – 4.4 mm




	Length	Straight/Straight (Female/Male)	Pinout	
4-Pin Double-Ended	0.5 m	BC-M8F4-M8M4-24-0.5		1 = Brown 2 = White 3 = Blue 4 = Black
	1 m	BC-M8F4-M8M4-24-1		
	2 m	BC-M8F4-M8M4-24-2		
	5 m	BC-M8F4-M8M4-24-5		
	8 m	BC-M8F4-M8M4-24-8		
	10 m	BC-M8F4-M8M4-24-10		
			24 AWG	Cable ø – 4.4 mm

*Not all models are shown. Please contact Banner for other available lengths and double-ended styles.

M8 Field Wireable Connectors

Temperature: -25° to +90 °C

Environmental Rating: IP67



3-Pin (Voltage: 30 V DC/AC, Current: 4 A)



	Straight	Right-Angle	Pinout
3-Pin Female Insulation Displacement	FIC-M8F3	FIC-M8F3A	 Female
3-Pin Male Insulation Displacement	FIC-M8F3A	FIC-M8M3A	
3-Pin Female Screw Terminal	FIC-M8F4	FIC-M8F4A	 Male
3-Pin Male Screw Terminal	FIC-M8M4	FIC-M8M4A	

1 = Brown
3 = Blue
4 = Black

22 AWG

4-Pin (Voltage: 30 V DC/AC, Current: 4 A)



	Straight	Right-Angle	Pinout
4-Pin Female Insulation Displacement	FIC-M8F4	FIC-M8F4A	 Female
4-Pin Male Insulation Displacement	FIC-M8M4	FIC-M8M4A	
4-Pin Female Screw Terminal	BFW-M8F4-4X	BFW-M8F4A-4X	 Male
4-Pin Male Screw Terminal	BFW-M8M4-4X	BFW-M8M4A-4X	


1 = Brown
2 = White
3 = Blue
4 = Black

22 AWG

M12 Field Wireable Connectors

Temperature: -40° to +85 °C

Environmental Rating: IP68



4-Pin (Voltage: 60 V DC/AC, Current: 4 A)



	Straight	Right-Angle	Pinout
4-Pin Female Screw Terminal	BFW-M12F4-6X	BFW-M12F4A-6X	1 = Brown 2 = White 3 = Blue 4 = Black
4-Pin Male Screw Terminal	BFW-M12M4-6X	BFW-M12M4A-6X	22 AWG

5-Pin (Voltage: 60 V DC/AC, Current: 4 A)



	Straight	Right-Angle	Pinout
5-Pin Female Screw Terminal	BFW-M12F5-6X	BFW-M12F5A-6X	1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
5-Pin Male Screw Terminal	BFW-M12M5-6X	BFW-M12M5A-6X	22 AWG

8-Pin (Voltage: 30 V DC/AC, Current: 2 A)




	Straight	Right-Angle	Pinout
8-Pin Female Screw Terminal	BFW-M12F8-8X	BFW-M12F8A-8X	1 = Brown 2 = Or/Bk 3 = Orange 4 = White 5 = Black 6 = Blue 7 = Gr/Ye 8 = Violet
8-Pin Male Screw Terminal	BFW-M12M8-8X	BFW-M12M8A-8X	22 AWG

M12 Field Wireable Slide Lock

Temperature: -40° to +85 °C

Environmental Rating: IP68



4-Pin (Voltage: 60 V DC/AC, Current: 4 A)



	Straight	Right-Angle	Pinout
4-Pin Female Slide Lock Terminal	BFW-M12F4-6SL	BFW-M12F4A-6SL	Female 1 = Brown 2 = White 3 = Blue 4 = Black
4-Pin Male Slide Lock Terminal	BFW-M12M4-6SL	BFW-M12M4A-6SL	Male 22 AWG

5-Pin (Voltage: 60 V DC/AC, Current: 4 A)



	Straight	Right-Angle	Pinout
5-Pin Female Slide Lock Terminal	BFW-M12F5-6SL	BFW-M12F5A-6SL	Female 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray
5-Pin Male Slide Lock Terminal	BFW-M12M5-6SL	BFW-M12M5A-6SL	Male 22 AWG

Smarter Automation. Better Solutions.™

Banner Engineering designs and manufactures industrial automation products including sensors, smart IIoT and industrial wireless technologies, LED lights and indicators, measurement devices, machine safety equipment, as well as barcode scanners and machine vision. These solutions help make many of the things we use every day, from food and medicine to cars and electronics. A high-quality, reliable Banner product is installed somewhere around the world every two seconds. Headquartered in Minneapolis since 1966, Banner is an industry leader with more than 10,000 products, operations on five continents, and a world-wide team of more than 5,500 employees and partners. Our dedication to innovation and personable service makes Banner a trusted source of smart automation technologies to customers around the globe.

