



Representative Image

Catalog No. 9T51B0144

Description: "1C,3kVA,133-120,80C,3R,60Hz,BB,AXF,QB"

UPC No 783173000113

Home > Transformers > Dry Type, Encapsulated, Enclosed > Buck Boost Autotransformer

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Buck Boost Autotransformer
GO Schedule	T5

Specifications

Phase	1
PriVoltage	133
SecVoltage	120
KVA	3.0 KVA
Coil Material	CU
TempRise	80.0 °C
ElecShield	N
Sub Type	Buck Boost Autotransformer
Frequency	60 Hz
Impedance	0.00 %
FrameSize	10200
Net Weight	16
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
EnergyEfficiency	None
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	16
Sound	Std
GSA Compliance	No

Classifications

UL	Yes
cUL	Yes
CE	No

Dimensions

Width	6.9 in
Depth	4.9 in
Height	8.4 in