

1529A Multi-Conductor - 300V Power-Limited Tray Cable



For more Information
please call

1-800-Belden1

**General Description:**

18 AWG pairs stranded (7x26) bare copper conductors, twisted pairs, PVC insulation, overall Beldfoil® shield (100% coverage), PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	# Pairs	AWG	Stranding	Conductor Material
	3	18	7x26	BC - Bare Copper
1		22	7x30	BC - Bare Copper

Total Number of Conductors: 7

Insulation**Insulation Material:**

Insulation Material
PVC - Polyvinyl Chloride

Outer Shield**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
18	7x26	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.3462

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 10.668 mm

Pair**Pair Color Code Chart:**

Number	Color
1	Black & White and Numbered 1
2	Black & White and Numbered 2
3	Black & White and Numbered 3
Communication	Orange

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +105°C

Bulk Cable Weight: 130.962 Kg/Km

Max. Recommended Pulling Tension: 733.953 N

Min. Bend Radius/Minor Axis: 106.680 mm

1529A Multi-Conductor - 300V Power-Limited Tray Cable

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG, ITC-ER, PLTC-ER
-------------------------	----------------------

CEC/C(UL) Specification:	CMG
--------------------------	-----

EU Directive 2011/65/EU (ROHS II):	Yes
------------------------------------	-----

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	UL1685 FT4 Loading
----------------	--------------------

CSA Flame Test:	FT4
-----------------	-----

IEEE Flame Test:	1202
------------------	------

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Suitability - Outdoor:	Yes
------------------------	-----

Suitability - Burial:	Yes
-----------------------	-----

Sunlight Resistance:	Yes
----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Surface Printing (Overall)

Surface Printing:	LEGEND: BELDEN 1529A E34972 3PR18 1C22 SHIELDED (UL) CMG 105C OR PLTC OR ITC SUN RES DIR BUR OR AWM 2464 80C 300V OR C(UL) CMG ----FT4 IEEE 1202 (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FEET
-------------------	---

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (μH/m)
0.571

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
114.835

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
177.174

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
19.2267

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
15.8472

Max. Operating Voltage - UL:

Voltage

1529A Multi-Conductor - 300V Power-Limited Tray Cable

300 V RMS

Notes (Overall)

Notes: Alternate color coding available upon request.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1529A 0107500	7,500 FT	757.500 LB	BLACK	C Z	3 PR #18 + 1 #22 PVC FS PVC

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 3 Revision Date: 05-17-2015

© 2019 Belden, Inc
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).