



Product: [1696A](#) 

Digital Audio Cable, 1 Pr #22, Str TC, Foil + Braid, PVC Jkt

Product Description

Digital Audio Cable, 1 Pair 22 AWG (7 x 30) Tinned Copper, Datalene® Insulation, Overall Beldfoil® Shield, 90% Tinned Copper Braid Shield, PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Digital audio, Interconnect between audio equipment such as microphones, speakers, amplifiers, mixing consoles
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code	Notes
Pair(s)	PE - Polyethylene (Foam)	0.027 in (0.69 mm)	0.082 in (2.1 mm)	Blue & White	HDPE

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC
Braid	Tinned Copper (TC)	90%	

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.025 in (0.64 mm)	0.235 in (5.97 mm)

Overall Cable Diameter (Nominal):	0.235 in (5.97 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Delay	Nom. Inductance	Nom. Velocity of Prop.	Max. Current
Pair(s)	18.2 Ohm/1000ft	13 pF/ft (43 pF/m)	26 pF/ft (85 pF/m)	110 Ohm	1.3 ns/ft	0.18 µH/ft (0.59 µH/m)	76%	6 Amps per conductor @ 30°C

Nom Outer Shield DCR@Cond DCR1-cnvc:	5.89 Ohm/1000ft (19.3 Ohm/km)
--------------------------------------	-------------------------------

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss (Attenuation)
0.384	0.58 dB/100ft
0.7056	0.69 dB/100ft
0.768	0.7 dB/100ft
1.024	0.76 dB/100ft
1.4112	0.82 dB/100ft
1.536	0.84 dB/100ft
2.048	0.88 dB/100ft
2.8224	0.93 dB/100ft
3.072	0.95 dB/100ft

4.096	1.09 dB/100ft
5.6448	1.32 dB/100ft
6.144	1.37 dB/100ft
8.192	1.48 dB/100ft
11.2896	1.74 dB/100ft
12.288	1.77 dB/100ft
24.576	2.41 dB/100ft

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-30°C to +60°C

Bend Radius

Stationary Min.	Installation Min.
2.4 in (61 mm)	2.4 in (61 mm)

Max. Pull Tension:	23.7 lbs (10.8 kg)
Bulk Cable Weight:	31 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	AES/EBU

Product Notes

Notes:	Cabling has two rod fillers for improved electrical performance.
--------	--

History

Update and Revision:	Revision Number: 0.479 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1696A B59250	Black, Matte	Reel	250 ft	612825121329	
1696A B59500	Black, Matte	Reel	500 ft	612825121336	
1696A B591000	Black, Matte	Reel	1,000 ft	612825121312	C
1696A B59U1000	Black, Matte	Reel	1,000 ft	612825121305	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.