

Product: [1924A](#) 



Audio Snake Cable, #24-24pr, BC, Individ. Shielded

Product Description

Audio Snake Cable, 24-24 AWG bare copper pairs, polyolefin insulation, individually shielded with double serve "French Braid", drain, numbered/color-coded PVC jackets, flexible PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Multi-channel interconnect between audio equipment such as microphones, speakers, amplifiers, mixing consoles; Live events or studio sound; Analog audio
------------------------	--

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
24	41x40	BC - Bare Copper	24

Insulation

Material	Nom. Insulation Diameter	Color Code
PP - Polypropylene	0.04 in (1.0 mm)	Brown, Red, Orange, Yellow, Green, Blue, Purple, Gray, White, Black, Tan, Pink, Gray/Brown, Gray/Red, Gray/Orange, Gray/Yellow, Gray/Green, Gray/Blue, Gray/Purple, Gray/Gray, Gray/White, Gray/Black, Gray/Tan, Gray/Pink
		Red and Black

Inner Shield

Shield Type	Material	Coverage
French Braid	Bare Copper (BC)	95%

Inner Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.119 in (3.02 mm)

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.825 in

Electrical Characteristics

Electricals

Nom. Characteristic Impedance
60 Ohm

Delay

Nom. Velocity of Prop.
66%

Voltage

UL Voltage Rating
300 V RMS

Mechanical Characteristics

Temperature

Operating	
-20°C To +60°C	
Max. Pull Tension:	700 lbs (320 kg)
Bulk Cable Weight:	397 lbs/1000ft (591 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.352 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
192A B59TEST	Black, Matte				
1924A B59500	Black, Matte	Reel	500 ft	612825126898	C
Footnote:	C - CRATE REEL PUT-UP.				

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.