



Product: [19364](#)

Portable Cordage, 3 C #14 Str BC, PVC Ins, PVC Jkt, UL Type SJT

[Request Sample](#)

Product Description

Portable Cordage, 3 Conductor 14AWG (41x30) Bare Copper, PVC Insulation, PVC Outer Jacket, UL Type SJT

Technical Specifications

Product Overview

Suitable Applications:	Portable cordage for supplying power to appliances and tools
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material	Notes
Conductor(s)	3	14 AWG	41x30	BC - Bare Copper	2.08mm2

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.033 in (0.84 mm)	0.141 in (3.58 mm)	Light Blue, Brown, Green/Yellow

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	20 AWG (7x28) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.042 in (1.1 mm)	0.402 in (10.2 mm)
Overall Cable Diameter (Nominal): 0.402 in (10.2 mm)		

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Max. Current
Conductor(s)	2.76 Ohm/1000ft	15 Amps per conductor @ 30°C

Voltage

UL Voltage Rating
300 V (Type SJT)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-20°C to +60°C

Bend Radius

Stationary Min.	Installation Min.
4.0 in (100 mm)	4.0 in (100 mm)

Max. Pull Tension:	172.5 lbs (78.24 kg)
Bulk Cable Weight:	97 lbs/1000ft

Standards and Compliance

NEC / UL Compliance:	SJT
AWM Compliance:	SJT
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.545 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
19364 010250	Black	Reel	250 ft	612825127017	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.