



Product: [31010](#) 

Lead Wire, #10 Str TC, XLPO Ins, UL TYPE SIS VW-1

 [Request Sample](#)

Product Description

Low Temp Rubber Lead Wire, 10AWG (65x28) Tinned Copper, XLPO Insulation, UL TYPE SIS VW-1 600V 90C

Technical Specifications

Product Overview

Suitable Applications:	for wiring switchboards, panelboards , distribution boards
------------------------	--

Construction Details

Conductor

Size	Stranding	Material
10	65x28	TC - Tinned Copper

Insulation

Material	Nom. Thickness
XLP, XLPO, XLPE (Thermoset)	0.033 in (0.84 mm)
XLP, XLPO, XLPE (Thermoset)	

Outer Jacket

Nom. Diameter
0.184 in

Electrical Characteristics

Voltage

UL Voltage Rating
600 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
90°C	-40°C to +90°C

Bend Radius

Stationary Min.	Installation Min.
0.74 in (19 mm)	0.74 in (19 mm)

Bulk Cable Weight:	47 lbs/1000ft (70 kg/km)
--------------------	--------------------------

Standards and Compliance

Flammability / Reaction to Fire:	VW-1
NEC / UL Compliance:	SIS
AWM Compliance:	N/A
Military Compliance:	N/A
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

APAC Compliance:	China RoHS II (GB/T 26572-2011)
------------------	---------------------------------

History

Update and Revision:	Revision Number: 0.385 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
31010 0082500	Gray	Reel	2,500 ft	612825141549	C U

Footnote:	C - CRATE REEL PUT-UP., U - TOPCOAT ADDERS ON STOCK SOLID COLORS. MINIMUM ORDER 10,000' PER COLOR COMBINATION. (SEE TOPCOAT ADDER TABLE)
-----------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.