



Product: [33390](#)

Lead Wire, #1/0 Str TC, Silicone Ins, AWM 3214

Request Sample

Product Description

Low Temp Rubber Lead Wire, 1/0AWG (262x24) Tinned Copper, Silicone Insulation, AWM 3214 CSA TYPE AWM 600V 150C

Technical Specifications

Product Overview

Suitable Applications:	Class 155(F) or Class 180(H) motor lead systems , high temperature applications, internal wiring of lighting fixtures and appliances
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
1/0	262x24	TC - Tinned Copper	1

Conductor Count:	1
------------------	---

Insulation

Material	Nominal Wall Thickness
Silicone Rubber	0.084 in

Electrical Characteristics

Voltage

UL Voltage Rating
600 V RMS

Temperature Range

Non-UL Temp Rating:	150°C
UL Temperature Rating:	150°C

Mechanical Characteristics

Recommended Maximum Baking Cycles:	24 Hours @ 410°F (210°C)
Bulk Cable Weight:	108.3 lbs/1000ft
Minimum Minor Axis Bend Radius:	2.38 in

Standards

UL AWM Style Compliance:	AWM 3214
CSA Rating:	600 V, 150°C
CSA AWM Compliance:	CSA AWM I B
CSA Type:	AWM

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes

EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

CSA Flammability:	FT2
UL voltage rating:	600 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
33390 010250	Black	Reel	250 ft	612825143499

Footnote:	C - CRATE REEL PUT-UP., F - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'.
-----------	--

Product Notes

Notes:	Recommended Maximum Baking Cycles: 24 hours @ 410°F (210°C)
--------	---

History

Update and Revision:	Revision Number: 0.362 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.