



Product: [5502G1](#)

Security & Sound, #22-1pr, #22-2c TC, Shielded Pair, CM, Water-Blocked

Product Description
Security & Sound Cable, Rated-CM, 1-22 AWG tinned copper pair with PVC insulation and a Beldfoil® shield, 2-22 AWG tinned copper conductors with PVC insulation, overall water resistant tape and PVC jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Noisy & Wet Location, Below-Grade Duct
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	22 AWG	7x30	TC - Tinned Copper
Conductor(s)	2	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.01 in (0.25 mm)	0.051 in (1.3 mm)	Black and Red
Conductor(s)	PVC - Polyvinyl Chloride	0.01 in (0.25 mm)	0.051 in (1.3 mm)	White, Green

Inner Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC
	No Shield		

Table Notes:	Waterblocking tape
--------------	--------------------

Outer Shield

Material	
No Shield	
Waterblocking:	Waterblock Tape

Outer Jacket

Separator	Material	Nom. Thickness	Nom. Diameter	Ripcord
Waterblocking Tape	PVC - Polyvinyl Chloride	0.025 in (0.64 mm)	0.234 in	Yes
Overall Cable Diameter (Nominal):	0.234 in			

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Pair(s)	16.4 Ohm/1000ft	14.5 Ohm/1000ft (47.6 Ohm/km)	44.5 pF/ft (146 pF/m)	80.1 pF/ft (263 pF/m)	4 Amps per Conductor at 25°C
Conductor(s)	17.9 Ohm/1000ft (58.7 Ohm/km)				4 Amps per Conductor at 25°C

Voltage

UL Voltage Rating

300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-40°C To +105°C

Bend Radius

Stationary Min.	Installation Min.
2.34 in (59.4 mm)	2.34 in

Max. Pull Tension:	42 lbs (19 kg)
Bulk Cable Weight:	25 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL1685 UL Loading
NEC / UL Compliance:	Article 800, CM
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.318 Revision Date: 05-31-2024
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
5502G1 0081000	Gray	612825163367	C
5502G1 008500	Gray	612825163374	

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.