



Product: [84316](#) 

Mil-Spec Coax, 50 Ohm, RG-316, 26 AWG Str SCCS, 95% SC Braid, FEP Jkt, Commercial Non-QPL

Product Description

Mil-Spec Coax, 50 Ohm, RG-316, 26 AWG (7x34) Silvered Copper Covered Steel Conductor, PTFE Insulation, 95% Silvered Copper Braid Shield, FEP Jacket, Commercial, non-QPL

Technical Specifications

Product Overview

Suitable Applications:	Aerospace wireless communication
------------------------	----------------------------------

Construction Details

RG Type:	316
----------	-----

Conductor

Size	Stranding	Nom. Diameter	Material
26 AWG	7x34	0.020 in	SCCS - Silvered Copper Covered Steel

Insulation

Material	Nom. Insulation Diameter	Color Code
PTFE - Polytetrafluoroethylene	0.060 in (1.5 mm)	White

Outer Shield

Layer	Outer Shield Type	Material	Coverage
1	Braid	Silvered Copper (SC)	95%

Outer Jacket

Material	Nom. Diameter
FEP - Fluorinated Ethylene Propylene	0.098 in (2.5 mm)

Overall Cable Diameter (Nominal):	0.098 in (2.5 mm)
-----------------------------------	-------------------

Electrical Characteristics

VSWR

Frequency	Max. VSWR
1 MHz - 3000 MHz	per M17/113-RG316

Attenuation

Frequency	Nom. Attenuation
1 MHz	1.2 dB/100ft
10 MHz	2.7 dB/100ft
50 MHz	5.6 dB/100ft
100 MHz	8.3 dB/100ft
200 MHz	12.0 dB/100ft
400 MHz	17.5 dB/100ft
700 MHz	23.7 dB/100ft
900 MHz	27.3 dB/100ft
1000 MHz	29.0 dB/100ft
1500 MHz	36.5 dB/100ft

2000 MHz	42.5 dB/100ft
2400 MHz	47.2 dB/100ft
3000 MHz	53.6 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
82.5 Ohm/1000ft (271 Ohm/km)	8.5 Ohm/1000ft (28 Ohm/km)	29 pF/ft (95 pF/m)	50 Ohm	70%

Voltage

Voltage Rating
900 V (Mil-Spec)

Mechanical Characteristics

Temperature

Operating
-70°C to +200°C

Bend Radius

Installation Min.
1 in (25 mm)

Max. Pull Tension:	27 lbs (12 kg)
Bulk Cable Weight:	10 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Aerial - When supported by messenger wire
Sustainability:	CA Prop 65
Military Compliance:	Commercial, non-QPL product (M17/113-RG316)
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.506 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
84316 001100	Brown	Reel	100 ft	612825207016	E
84316 001500	Brown	Reel	500 ft	612825207139	E
84316 0011000	Brown	Reel	1,000 ft	612825207023	E

Footnote:	E - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'.
-----------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.