

Product: [8786](#) 



Audio, Control and Instrumentation, 4 Conductor 24 AWG, Shielded; 2 Conductor 22 AWG Unshielded, CM

Product Description

4 Conductor 24 AWG stranded (7x32) and 2 Conductor 22 AWG stranded (7x30) TC conductors, PVC insulation, (4) conductors cabled, 22 AWG stranded TC drain wire, CM PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	24 AWG	7x32	TC - Tinned Copper
Conductor(s)	2	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.0155 in (0.394 mm)	0.054 in (1.4 mm)	Blue Quad, Blue, White
Conductor(s)	PVC - Polyvinyl Chloride	0.0155 in (0.394 mm)	0.060 in (1.5 mm)	Black, Green, Red, Yellow, Blue Beldfoil®, Blue, White, Unshielded

Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type
Over Quad	Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC

Outer Shield

Material
No Shield

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.028 in (0.71 mm)	0.236 in

Overall Cable Diameter (Nominal):	0.236 in.
-----------------------------------	-----------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Velocity of Prop.	Max. Current
32.1 Ohm/1000ft	11.9 Ohm/1000ft (39.0 Ohm/km)	65%	1.5 Amps per Conductor at 25°C (24 AWG)
15 Ohm/1000ft (49 Ohm/km)			3 Amps per Conductor at 25°C (22 AWG)

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
90°C	-20°C To +90°C

Bend Radius

Stationary Min.	Installation Min.
2.36 in (59.9 mm)	2.36 in

Max. Pull Tension:	49.3 lbs (22.4 kg)
Bulk Cable Weight:	30 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	UL 1685 UL Loading
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CM
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Inner Beldfoil« shield over 24 AWG quads. (4) conductors cabled under 100% Beldfoil« shield; (2) conductors unshielded. Quad connection scheme: The black & red wires (or wires directly opposite one another) are connected together to form one conductor, and similarly the green & yellow wires (or remaining wires) are connected together to form the second conductor.
--------	---

History

Update and Revision:	Revision Number: 0.363 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8786 060500	Chrome	Reel	500 ft	612825216377	C
8786 060U500	Chrome	UnReel	500 ft	612825216407	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.