

**Product: [88241](#)**

Analog Video, RG59, #23 Solid BCCS, 95% BC Braid, FEP Jacket, CMP


**Product Description**

23 AWG Solid .023" bare copper-covered steel conductor, plenum, FEP insulation, bare copper braid shield (95% coverage), FEP jacket.

**Technical Specifications**
**Product Overview**

Suitable Applications:	Standard analog video
------------------------	-----------------------

**Construction Details**

RG Type:	59
----------	----

**Conductor**

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	23 AWG	Solid	0.023 in	BCCS - Bare Copper Covered Steel

**Insulation**

Material	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene	0.132 in (3.35 mm)	Clear

**Outer Shield**

Outer Shield Type	Material	Coverage
Braid	Bare Copper (BC)	95%

**Outer Jacket**

Material	Nom. Diameter
FEP - Fluorinated Ethylene Propylene	0.190 in (4.83 mm)

Overall Cable Diameter (Nominal): 0.190 in (4.83 mm)

**Electrical Characteristics**
**Attenuation**

Frequency	Nom. Attenuation
1 MHz	0.5 dB/100ft
10 MHz	1 dB/100ft
50 MHz	2.3 dB/100ft
100 MHz	3.3 dB/100ft
200 MHz	5.2 dB/100ft
400 MHz	8.4 dB/100ft
700 MHz	11.6 dB/100ft
900 MHz	13.8 dB/100ft
1000 MHz	14.8 dB/100ft

**Electricals**

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
49 Ohm/1000ft (160 Ohm/km)	2.6 Ohm/1000ft (8.5 Ohm/km)	19.5 pF/ft (64.0 pF/m)	75 Ohm	70%

**Voltage**

UL Voltage Rating	Voltage Rating
300 V RMS	1700 V RMS

## Mechanical Characteristics

### Temperature

UL Temperature	Operating
200°C	-70°C To +200°C

### Bend Radius

Stationary Min.	Installation Min.
1.9 in (48 mm)	1.9 in (48 mm)

Max. Pull Tension: 70 lbs (32 kg)

Bulk Cable Weight: 37 lbs/1000ft (55 kg/km)

## Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Burial
Flammability / Reaction to Fire:	NFPA 262, FT6, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	8241

## History

Update and Revision: Revision Number: 0.596 Revision Date: 12-18-2025

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
88241 010500	Black	Reel	500 ft	612825216957	C
88241 0101000	Black	Reel	1,000 ft	612825216933	C

Footnote: C - CRATE REEL PUT-UP.

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.