



Product: [9309](#) 

Audio, Control & Instrument, #22-9pr, PVC, O/A Foil, PVC Jkt, CMG

Product Description

Audio, Control & Instrument Cable, 22 AWG solid tinned copper conductors, PVC insulation, twisted pairs, overall Beldfoil® shield (100% coverage), 22 AWG stranded tinned copper drain wire, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	9	22 AWG	Solid	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.013 in (0.33 mm)	0.052 in (1.3 mm)	Black & Red, Black & White, Black & Green, Black & Blue, Black & Yellow, Black & Brown, Black & Orange, Red & White, Red & Green

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.033 in (0.84 mm)	0.363 in

Overall Cable Diameter (Nominal):	0.363 in
-----------------------------------	----------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Inductance	Max. Current
20.6 Ohm/1000ft	35 pF/ft (110 pF/m)	50 pF/ft (160 pF/m)	0.02 µH/ft (0.066 µH/m)	3.6 Amps per Conductor at 30°C

Nom Outer Shield DCR@Cond DCR1-cnvc:	10.4 Ohm/1000ft (34.1 Ohm/km)
--------------------------------------	-------------------------------

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
80°C	-20°C to +80°C

Bend Radius

Stationary Min.	Installation Min.
3.63 in (92.2 mm)	3.63 in

Max. Pull Tension:	149 lbs (67.6 kg)
Bulk Cable Weight:	79 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL1685 FT4 Loading, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.337 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9309 060500	Chrome	Reel	500 ft	612825227588	C
9309 0601000	Chrome	Reel	1,000 ft	612825227571	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.