



Product: [9451DP](#)

Line Level Audio Cable, 2 Parallel Pr #22 Str TC, O/A Foil, Flamarrest® Jkt, CMP

Product Description

Line Level Audio Cable, 2 Parallel Pair 22 AWG (7 x 30) Tinned Copper, FEP insulation, Overall Beldfoil® Shield, Flamarrest® Jacket, CMP

Technical Specifications

Product Overview

Suitable Applications:	Line level audio; Low voltage analog signals and control
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	2	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	FEP - Fluorinated Ethylene Propylene	0.008 in (0.20 mm)	0.044 in (1.1 mm)	Black & Red, Black & White

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.127 in (3.23 mm)

Outer Jacket1 Table Notes: Jacket and shield are bonded so both can be removed on automatic stripping equipment. Drain wire is inside foil shield.

Overall Cable Diameter (Nominal): 0.269 in (6.83 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Delay	Nom. Inductance	Nom. Velocity of Prop.	Max. Current
Pair(s)	18.2 Ohm/1000ft	35 pF/ft (110 pF/m)	67 pF/ft (220 pF/m)	42 Ohm	1.47 ns/ft	0.15 μ H/ft (0.49 μ H/m)	69%	2.8 Amps per Conductor at 25°C
Nom Outer Shield DCR:		13.93 Ohm/1000ft (45.70 Ohm/km)						

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-20°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
1.3 in (33 mm)	1.3 in (33 mm)

Max. Pull Tension:	45.5 lbs (20.6 kg)
Bulk Cable Weight:	24 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262 (UL910), FT6
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	9451D

History

Update and Revision:	Revision Number: 0.484 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9451DP 009Z250	White	ReelTuff Box	250 ft	612825439363	
9451DP 009500	White	Reel	500 ft	612825353249	
9451DP 009Z500	White	ReelTuff Box	500 ft	612825439370	
9451DP 009Z750	White	ReelTuff Box	750 ft	612825252894	
9451DP 0091000	White	Reel	1,000 ft	612825433958	C
9451DP 009Z1000	White	ReelTuff Box	1,000 ft	612825439301	
9451DP 0095000	White	Reel	5,000 ft	612825435174	
9451DP 00910000	White	Reel	10,000 ft	612825377030	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.