



Product: [9565](#) 

High Perform Instr, 15 Pr #18 Str TC, PVC Ins E2, OS, PVC Jkt, PLTC

 [Request Sample](#)

Product Description

High Performance Instrumentation, 15 Pair 18AWG (19x30) Tinned Copper, PVC Insulation E2 Color Code, Overall Beldfoil® Shield, PVC Outer Jacket, PLTC

Technical Specifications

Product Overview

Suitable Applications:	Industrial Control, Raceways Cable trays and ducts, Digital Control, Instruments (4-20ma, 0-10v, ...), low voltage digital control (24v, ...), encoders, control circuits, distributed control
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	15	18	19x30	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.078 in (2.0 mm)	Black, Red and Numbered

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (7x26) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.063 in (1.6 mm)	0.739 in (18.8 mm)	Yes

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Inductance	Max. Current
7.19 Ohm/1000ft	35 pF/ft (110 pF/m)	54 pF/ft (180 pF/m)	0.17 µH/ft (0.56 µH/m)	7 Amps per Conductor at 25°C

Nom Outer Shield DCR@Cond DCR1-cnvr:	0.81 Ohm/1000ft (2.7 Ohm/km)
---	------------------------------

Voltage

UL Voltage Rating
300 V (PLTC)

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-30°C To +105°C

Bend Radius

Stationary Min.	Installation Min.
7.39 in (188 mm)	7.39 in (188 mm)

Max. Pull Tension:	763.4 lbs (346.3 kg)
Bulk Cable Weight:	309 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Burial
Flammability / Reaction to Fire:	UL 1685 FT4 loading, FT4, T-29-520, IEEE 1202 FT4
NEC / UL Compliance:	Article 725, Article 727, Article 800, CMG, ITC, PLTC
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.590 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
9565 0601000	Chrome	612825256007	C
9565 060500	Chrome	612825256014	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.