



**Product:** BRS20-4TX/2SFP

**Configurator:** BRS20-4TX/2SFP

### Configurator Description

The Hirschmann BOBCAT Switch is the first of its kind to enable real-time communication using TSN. To effectively support the increasing real-time communication requirements in industrial settings, a strong Ethernet network backbone is essential. This compact managed switches allow for expanded bandwidth capabilities by adjusting your SFPs from 1 to 2.5 Gigabit – requiring no change to the appliance.

### Technical Specifications

#### Product description

|                        |                                                                                                                                             |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------|
| Type                   | BRS20-4TX/2SFP (Product code: BRS20-0600Z6Z6-STCY99HHSESXX.X.XX)                                                                            |
| Description            | Managed Industrial Switch for DIN Rail, fanless design Fast Ethernet Type                                                                   |
| Software Version       | HiOS10.0.00                                                                                                                                 |
| Part Number            | 942170021                                                                                                                                   |
| Port type and quantity | 6 Ports in total: 4x 10/100BASE TX / RJ45; 2x 100Mbit/s fiber ; 1. Uplink: 1 x SFP Slot (100 Mbit/s) ; 2. Uplink: 1 x SFP Slot (100 Mbit/s) |

#### More Interfaces

|                                         |                                   |
|-----------------------------------------|-----------------------------------|
| Power supply/signaling contact          | 1 x plug-in terminal block, 6-pin |
| Digital Input                           | 1 x plug-in terminal block, 2-pin |
| Local Management and Device Replacement | USB-C                             |

#### Network size - length of cable

|                                                               |                                             |
|---------------------------------------------------------------|---------------------------------------------|
| Twisted pair (TP)                                             | 0 - 100 m                                   |
| Single mode fiber (SM)<br>9/125 µm                            | see SFP fiber modules see SFP fiber modules |
| Single mode fiber (LH)<br>9/125 µm (long haul<br>transceiver) | see SFP fiber modules see SFP fiber modules |
| Multimode fiber (MM)<br>50/125 µm                             | see SFP fiber modules see SFP fiber modules |
| Multimode fiber (MM)<br>62.5/125 µm                           | see SFP fiber modules see SFP fiber modules |

#### Network size - cascading

|                        |     |
|------------------------|-----|
| Line - / star topology | any |
|------------------------|-----|

#### Power requirements

|                               |                       |
|-------------------------------|-----------------------|
| Operating Voltage             | 2 x 12 VDC ... 24 VDC |
| Power consumption             | 7 W                   |
| Power output in BTU<br>(IT)/h | 24                    |

#### Software

|            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Switching  | CoS Queue Management, Egress Interface Shaping, Fast Aging, Flow Control (802.3X), GARP Multicast Registration Protocol (GMRP), GARP VLAN Registration Protocol (GVRP), IGMP Snooping/Querier per VLAN (v1/v2/v3), Independent VLAN Learning, Ingress Storm Protection, Interface Trust Mode, Jumbo Frames, Multiple MAC Registration Protocol (MMRP), Multiple Registration Protocol (MRP), Multiple VLAN Registration Protocol (MVRP), QoS / Port Prioritization (802.1D/p), Queue-Shaping / Max. Queue Bandwidth, Static Unicast/Multicast Address Entries, TOS/DSCP Prioritization, Unknown Multicast Filtering, VLAN (802.1Q), Voice VLAN |
| Redundancy | High Availability Seamless Redundancy Protocol (HSR) (IEC62439-3), Link Aggregation with LACP, Link Backup, MRP over Link Aggregation, MSTP (802.1Q), RSTP (Rapid Spanning Tree Protocol), RSTP 802.1D-2004, RSTP Guards                                                                                                                                                                                                                                                                                                                                                                                                                       |

|                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
|----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Management           | Dual Software Image Support, TFTP, SFTP, SCP, LLDP (802.1AB), LLDP-MED, SSHv2, HTTP, HTTPS, Traps, SNMP v1/v2/v3, Telnet, IPv6 Management                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Diagnostics          | Management Address Conflict Detection, MAC Notification, Signal Contact, Device Status Indication, TCPDump, LEDs, Syslog, Persistent Logging on ACA, Port Monitoring with Auto-Disable, Link Flap Detection, Overload Detection, Duplex Mismatch Detection, Link Speed and Duplex Monitoring, RMON (1,2,3,9), Port Mirroring 1:1, Port Mirroring 8:1, Port Mirroring N:1, Port Mirroring N:2, System Information, Self-Tests on Cold Start, Copper Cable Test, SFP Management, Configuration Check Dialog, Switch Dump                                                                                                                                                                                                            |
| Configuration        | Automatic Configuration Undo (roll-back), Configuration Fingerprint, Text-based Configuration File (XML), Backup config on a remote server when saving, Clear config but keep IP settings, BOOTP/DHCP Client with Auto-Configuration, DHCP Server: per Port, DHCP Server: Pools per VLAN, AutoConfiguration Adapter ACA21/22 (USB), HiDiscovery, USB-C Management support, Command Line Interface (CLI), CLI Scripting, CLI script handling over ENVM at boot, Full-featured MIB Support, Context-sensitive Help, HTML5 based Management                                                                                                                                                                                          |
| Security             | ISASecure CSA / IEC 62443-4-2 certified, MAC-based Port Security, Port-based Access Control with 802.1X, Guest/unauthenticated VLAN, Integrated Authentication Server (IAS), RADIUS VLAN Assignment, Denial-of-Service Prevention, DoS Prevention Drop Counter, VLAN-based ACL, Ingress VLAN-based ACL, Basic ACL, Access to Management restricted by VLAN, Device Security Indication, Audit Trail, CLI Logging, HTTPS Certificate Management, Restricted Management Access, Appropriate Use Banner, Configurable Password Policy, Configurable Number of Login Attempts, SNMP Logging, Multiple Privilege Levels, Local User Management, Remote Authentication via RADIUS, User Account Locking, Password change on first login |
| Time synchronisation | PTPv2 Transparent Clock two-step, PTPv2 Boundary Clock, BC with Up to 8 Sync / s , 802.1AS, Buffered Real Time Clock, SNTP Client, SNTP Server                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Industrial Profiles  | EtherNet/IP Protocol, IEC61850 Protocol (MMS Server, Switch Model), Modbus TCP, PROFINET Protocol                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Miscellaneous        | Digital IO Management, Manual Cable Crossing, Port Power Down                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |

Ambient conditions

|                                         |             |
|-----------------------------------------|-------------|
| MTBF (Telecordia SR-332 Issue 3) @ 25°C | 5 720 732 h |
| Operating temperature                   | 0-+60       |
| Storage/transport temperature           | -40-+70 °C  |
| Relative humidity (non-condensing)      | 1- 95 %     |

Mechanical construction

|                    |                         |
|--------------------|-------------------------|
| Dimensions (WxHxD) | 57 mm x 138 mm x 115 mm |
| Weight             | 420 g                   |
| Housing            | PC-ABS                  |
| Mounting           | DIN Rail                |
| Protection class   | IP30                    |

Mechanical stability

|                         |                                                                                                                                        |
|-------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| IEC 60068-2-6 vibration | 5 Hz ... 8,4 Hz with 3,5 mm amplitude; 2 Hz ... 13,2 Hz with 1 mm amplitude; 8,4 Hz ... 200 Hz with 1 g; 13,2 Hz ... 100 Hz with 0,7 g |
| IEC 60068-2-27 shock    | 15 g, 11 ms duration                                                                                                                   |

EMC interference immunity

|                                            |                                                                     |
|--------------------------------------------|---------------------------------------------------------------------|
| EN 61000-4-2 electrostatic discharge (ESD) | 6 kV contact discharge, 8 kV air discharge                          |
| EN 61000-4-3 electromagnetic field         | 10 V/m (80-2000 MHz); 5 V/m (2000-2700 MHz); 3 V/m (5100-6000 MHz)  |
| EN 61000-4-4 fast transients (burst)       | 2 kV power line, 2 kV data line                                     |
| EN 61000-4-5 surge voltage                 | power line: 2 kV (line/earth) and 1 kV (line/line); data line: 2 kV |
| EN 61000-4-6 Conducted Immunity            | 10 V (150 kHz-80 MHz)                                               |

EMC emitted immunity

|                   |                            |
|-------------------|----------------------------|
| EN 55022          | EN 55032 Class A           |
| FCC CFR47 Part 15 | FCC 47CFR Part 15, Class A |

Approvals

|                                        |                             |
|----------------------------------------|-----------------------------|
| Basis Standard                         | CE, FCC, EN61131, EN62368-1 |
| Safety of industrial control equipment | cUL61010                    |

Reliability

|           |                                                                             |
|-----------|-----------------------------------------------------------------------------|
| Guarantee | 60 months (please refer to the terms of guarantee for detailed information) |
|-----------|-----------------------------------------------------------------------------|

Scope of delivery and accessories

|                   |                                                                                                                                                                                                                                                |
|-------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Accessories       | AutoConfiguration Adapter ACA22-USB-C (EEC) 942239001; 6-pin terminal block with screw lock (50 pieces) 943 845-013; 2-pin terminal block with screw lock (50 pieces) 943 845-009; Industrial HiVision Network Management Software 943 156-xxx |
| Scope of delivery | 1 × Device, 1 × Safety and general information sheet, 1 × Terminal block for supply voltage and signal contact, 1 × Terminal block for the digital input depending on device variant, 2 × Ferrites with key depending on device variant        |

Further Instructions

|                       |                                                                                                                           |
|-----------------------|---------------------------------------------------------------------------------------------------------------------------|
| Product Documentation | <a href="https://www.doc.hirschmann.com/index.html">https://www.doc.hirschmann.com/index.html</a>                         |
| Certificates          | <a href="https://www.doc.hirschmann.com/certificates.html">https://www.doc.hirschmann.com/certificates.html</a>           |
| Software Download     | <a href="https://hirschmann-support.belden.com/en-US/downloads">https://hirschmann-support.belden.com/en-US/downloads</a> |

© 2025 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.