

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	15[mm]
Max. Air Flow:	26.8[CFM]
Max. Air Flow:	0.76[m3 per min]
Max. Static Pressure:	0.09[In H2O]
Max. Static Pressure:	23.5[Pa]
Fan Speed:	2500[RPM]
Noise:	27.5[dB]
Life Expectancy:	40 degree C 40,000 Hours[L10]
Bearing Type:	Sleeve Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.11[A]
Input Power:	1.3[W]
Mass:	55[g]
Tach / Locked Rotor Output:	Locked Rotor
Status:	Active