

Detailed Specifications

Frame Width:	35[mm]
Frame Height:	35[mm]
Frame Length:	15.5[mm]
Steps per Rev.:	48
Step Angle:	7.5[degrees]
Drive Sequence:	bipolar constant current
Drive Voltage:	24[V]
Rated Current per Phase:	600[A]
Resistance:	5.5[Ohms]
Magnet Type:	MS70
Magnet Material:	bonded Nd-Fe-B
Holding Torque:	32[mN per m]
Max Speed:	2400[pps]
Max Speed:	3000[rpm]