





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		REVISED COLOR	5/16/11	



RECOMMENDED
PCB LAYOUT
PCB THICKNESS .031 [0.8mm]

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 1 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.

A=.049 [1.25] X No. of Spaces
B=.049 [1.25] X No. of Spaces + .070 [1.80]
C=.049 [1.25] X No. of Spaces + .118 [3.00]
D=.049 [1.25] X No. of Spaces + .251 [6.40]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MX 1.25mm WAFER SMT RIGHT ANGLE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				ADAM TECH			
.X ± .10 .XX ± .020 .XXX ± .015	ØX ± .10 ØXX ± .015 ØXXX ± .010			909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
APPROVALS		DATE		TITLE MX 1.25mm WAFER SMT RIGHT ANGLE			
DRAWN	BW	01/17/07		SIZE PART NO.			
CHECKED				125SH-A-XX-TR-SMT			
APPROVED				REV. A			
REF:	X	SCALE: NTS	SHEET 1 OF 1				