





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/04/09	
A		UPDATED SPECS	8/5/09	
B		REVISED SPEC.	3/15/12	



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Natural (Ivory)

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Voltage rating: 50 AC/DC

Current rating: 0.7 AC/DC

Contact resistance: 20 mohms max

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 13

A=.060 [1.50] X No. of Spaces

B=.060 [1.50] X No. of Positions + .118 [3.00]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	DY	8/04/09
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.059 [1.50] TOP ENTRY TYPE, SMT TYPE

SIZE X	PART NO. 15SH-A-XX-TS-SMT	REV. B
REF: S00123T	SCALE: NTS	SHEET 1 OF 1