





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/10/09	
A		REVISED DIM.	7/07/10	
B		REVISED SPEC.	05/15/12	



Recommended PCB Layout



SPECIFICATIONS:

Material:
Insulator: Nylon66, rated UL 94V-0
Insulator color: Beige
Contacts: Brass
Plating:
Tin over copper underplate overall.
Electrical:
Operating voltage: 250 VAC max
Current rating: 3 Amps max
Contact resistance: 20 mohms max
Dielectric withstanding voltage: 1000 VAC for 1 minute
Mechanical:
Temperature Rating:
Operating temperature: -40°C to +105°C
Environmental:
Lead free, RoHS compliant

Positions: 02 thru 20
A = .098 [2.50] x No. of Spaces
B = .098 [2.50] x No. of Spaces + .197 [5.00]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		INCHES		HOLES	
.X	± .10	ØXX	± .10	.X	± .10
.XX	± .020	ØXXX	± .015	.XX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .010
APPROVALS		DATE			
DRAWN	DR	1/10/09			
CHECKED					
APPROVED					
TITLE		SIZE		PART NO.	
.098 [2.50] PITCH WAFER, STRAIGHT PCB		X		25SH-E-XX-TS	
LOW PROFILE		REF: S00123T		SCALE: NTS	
				SHEET 1 OF 1	
				REV. B	

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710