



APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

| Rev | AWO# | Description       | Date    | Appr |
|-----|------|-------------------|---------|------|
| -   |      | RELEASED          | 5/27/05 |      |
| A   |      | CHANGED TERMINALS | 9/02/09 |      |
| B   |      | CHANGED TERMINALS | 5/06/11 |      |



RECOMMENDED PCB LAYOUT

Positions: 02 thru 80  
 A = .079 [2.00] x No. of Positions per Row  
 B = .079 [2.00] x No. of Spaces

SPECIFICATIONS:  
 Material: Nylon, rated UL 94V-0  
 Insulator color: Black  
 Contacts: Phosphor Bronze  
 Plating: Gold flash over Nickel underplate overall  
 Electrical:  
 Current rating: 1 Amp max.  
 Contact resistance: 20 mohms max. initial  
 Insulation resistance: 5,000 Mohms min.  
 Dielectric withstand voltage: 500 VAC for 1 minute  
 Temperature Rating:  
 Operating temperature: -40°C to +105°C  
 Environmental:  
 Lead free, RoHS compliant

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710  
 TITLE: .079 x .079 DUAL ROW RECEPTACLE STRIP  
 .169 [4.30] HEIGHT, GOLD PLATED

**A**

| APPROVALS |      | DRAWN | SS | 5/27/05 | SIZE | PART NO.    | REV.       |
|-----------|------|-------|----|---------|------|-------------|------------|
| CHECKED   | REF. |       |    |         |      |             |            |
|           | X    |       |    |         |      | 2RS2-XX-G   | B          |
| APPROVED  |      |       |    |         |      | REF: SD005T | SCALE: NTS |