







#4-40 X 7/16" FILLISTER HEAD MACHINE SCREW
MATERIAL - STEEL
FINISH - BRIGHT ZINC (HEXAVALENT CHROMIUM FREE)
QTY: 2 EACH



#4-40 #2 BLANK HEX NUT
MATERIAL - STEEL
FINISH - BRIGHT ZINC (HEXAVALENT CHROMIUM FREE)
QTY: 2 EACH



#4-40 X 1/2" FILLISTER HEAD CAPTIVE SCREW
MATERIAL - STEEL
FINISH - BRIGHT ZINC (HEXAVALENT CHROMIUM FREE)
QTY: 2 EACH



#4 SADDLE WASHER
MATERIAL - STEEL
FINISH - BRIGHT ZINC (HEXAVALENT CHROMIUM FREE)
QTY: 2 EACH

THIS IS A CONTROLLED DOCUMENT AND IS
SUBJECT TO CHANGE. CONTACT NORTHERN
TECHNOLOGIES ENGINEERING FOR THE
LATEST REVISION.

REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED
	A	ECN 0607	10-AUG-06	
	B	ECN 0845	19-FEB-24	



PART NUMBER INFORMATION
COLOR: BLACK

PART#	LOGO STYLE	SUPPLIED
A30E310004	NO LOGO	BULK
C88E310004	NO LOGO	PACKAGED
A30E311004	NORTECH LOGO	BULK
C88E311004	NORTECH LOGO	PACKAGED

COLOR: GRAY - DISCONTINUED

PART#	LOGO STYLE	SUPPLIED
A30E310005	NO LOGO	DISCONTINUED
C88E310005	NO LOGO	DISCONTINUED
A30E311005	NORTECH LOGO	DISCONTINUED
C88E311005	NORTECH LOGO	DISCONTINUED

CONNECTOR COVER:
1.MATERIAL: THERMOPLASTIC UL94V-0
2.COLOR: BLACK
3.DIMENSIONS: INCHES [MM]
4.TOLERANCE: ±0.015 [0.381]

JACKET INSERT TREE
1.MATERIAL: POLYPROPYLENE HOMOPOLYMER
2.COLOR: BLACK
3.DIMENSIONS: INCHES [MM]
4.TOLERANCE: ±0.010 [0.254]

UNLESS OTHERWISE SPECIFIED		Northern Technologies			
1. ALL DIMENSIONS ARE IN INCHES (MM) 2. DIMENSIONS ARE TYPICAL		THIS DRAWING IS THE PROPERTY OF NORTHERN TECHNOLOGIES AND SHOULD NOT BE REPRODUCED WITHOUT NORTHERN TECHNOLOGIES WRITTEN PERMISSION.			
DRAWN JSD		PART NUMBER SEE PART NUMBER INFORMATION			
CHECKED SCN		DESCRIPTION CPP 15 STR EXIT TWO PIECE PLASTIC COVER			
ISSUED		SIZE B	CODE 200_123	DWG NO. 0002-200-123	REV B
		SCALE 1:1		SHEET 1 OF 1	