




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/25/05	
A		REVISED SPEC.	03/04/13	



Unit: Inch / mm

Positions	DIMENSIONS			
	A	B	C	D
9	.666 [16.92]	.984 [24.99]	1.213 [30.81]	.883 [22.44]
15	.994 [25.25]	1.312 [33.32]	1.541 [39.14]	1.213 [30.81]
25	1.534 [38.96]	1.852 [47.04]	2.088 [53.04]	1.755 [44.57]
37	2.182 [55.43]	2.500 [63.50]	2.729 [69.32]	2.414 [61.32]

SPECIFICATIONS:
Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Shell: Steel, Tin plated
Plating:
Gold Flash over Nickel underplate on mating area,
Tin over Copper underplate on IDC area
Electrical:
Operating voltage: 250 VAC max
Current rating: 3 Amps max
Contact resistance: 15 mohms max
Insulation resistance: 3,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Mechanical:
Recommended cable size: 28-30 AWG
Temperature Rating:
Operating temperature: -55°C to +125°C
Environmental:
Lead free, RoHS compliant

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

IDC FLAT CABLE D-SUB PLUG
METAL SHELL, .130 [3.30] MOUNTING HOLES

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				ADAM TECH			
.X ± .10	ØX ± .10	DATE		909 Rahway Avenue, Union, NJ 07083			
.XX ± .020	ØXX ± .015			Phone: 908-687-5000 Fax: 908-687-5710			
.XXX ± .015	ØXXX ± .010			TITLE			
APPROVALS				IDC FLAT CABLE D-SUB PLUG			
DRAWN	SS	4/25/05		METAL SHELL, .130 [3.30] MOUNTING HOLES			
CHECKED				SIZE		PART NO.	REV.
APPROVED				X		DXXX-PF-M1	A
REF.	S0003T	SCALE	NIS	SHEET	1 OF 1		

SPECIFICATIONS:
Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Shell: Steel, Tin plated
Plating:
Gold Flash over Nickel underplate on mating area,
Tin over Copper underplate on IDC area
Electrical:
Operating voltage: 250 VAC max
Current rating: 3 Amps max
Contact resistance: 15 mohms max
Insulation resistance: 3,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Mechanical:
Recommended cable size: 28-30 AWG
Temperature Rating:
Operating temperature: -55°C to +125°C
Environmental:
Lead free, RoHS compliant