



L-Com's Networking Cabinet is a versatile solution for organizing and securing your rack-mounted networking equipment

These cabinets can be selfstanding or wall-mounted when floor space is at a minimum. Cabinets are available in a variety of heights

Model / SKU Number	L	_C-SMA6406	LC-SMA6606	LC-SMA6409	LC-SMA6609	LC-SMA6412	LC-SMA6612	LC-SMA6415	LC-SMA6615	LC-SMA6418	LC-SMA6618	LC-SMA662
PHYSICAL												
Rack Capacity (in Rack Units)		6U	6U	9U	9U	12U	12U	15U	15U	18U	18U	22U
Depth		450mm	600mm	450mm	600mm	450mm	600mm	450mm	600mm	450mm	600mm	600mm
Unit Dimensions (in)	Н	14.75	14.75	20	20	24.4	25.25	31	31	34.92	36	43
	W	23.63	23.63	23.63	23.63	21.65	23.63	23.63	23.63	21.65	23.63	23.63
	D	17.72	23.63	17.72	23.63	17.72	23.63	17.72	23.63	17.72	23.63	23.63
Maximum Rail Depth (in)		15.5	20.5	15.5	21.5	11.75	21.5	15.5	21.5	11.75	21.5	21.5
Weight Capacity (kg / lbs)							59 / 130					
Painting / Coating		Black Powder Coat										
Material		Cold Rolled Steel (1.2mm) Welded Frame Structure										
Door		Tempered Glass Door - Clear/Reversible										
Interior Rails Mounting	Square unthreaded cage nut opening											
ADDITIONAL FEATURES / INFORM	ATION											
Casters		Casters included with LC-SMA6415, LC-SMA6615, LC-SMA6622										
Cable Management		Top and bottom covers screw on and off (replaceable)										
Security		Locks included for door and side panels										
Cooling		Cabinet has laser cut-outs for optional fan installation (purchased separately)										
Shelving		Includes one set of "L" brackets										
Mounting		Mounting bar included										
Assembly		Assembly required										
COMPLIANCE												
RoHS							✓					
CE		√										
HIPPA		·										
PCI		✓										
EIA/ECA-310-E Compliant		√										
NEMA Rated Type 1		✓										
IP20 Protection Grade							✓					
SHIPPING												
Shipping Dimensions (in)	L	25	25	25	25	26	26	31	31	37	37	45
	W	19	25	21	25	25	25	25	25	25	25	25
	Н	13	13	14	13	10	13	9	13	10	13	13
Shipping Weight (lbs)		41	52	48	58	45	65	64	77	72	77	102