








APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/5/19	



SPECIFICATIONS:

Material:

Housing: Nylon 46, rated UL 94V-0, Color: Black

Contacts: Brass, Gold Flash over Nickel

Shell: Zinc Alloy, Nickel plated

Spring: Stainless Steel

Washer: Phosphor Bronze, Nickel plated

Nut: Brass, Nickel plated

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	LH	9/5/19
CHECKED	RC	9/5/19
APPROVED		

ADAM
TECH
 INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE
 WATERPROOF CONNECTOR, MALE DIN,
 REAR PANEL, SHELL LOCK TYPE, STR PCB

SIZE	PART NO.	REV.
X	SD-PNNXX-MMLRH-P00-000	-
REF: S00298T	SCALE: NTS	SHEET 1 OF 1